



SCHUNK chuck jaws for HO 7 MA 12



Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	55 - 134	312	SZAJ 25-9	0138115	18	40	58	25	M6	30	M14	Steel	2.7
	97 - 176	312	SZAJ 25-10	0138129	18	40	58	25	M6	30	M14	Steel	2.3
	139 - 218	314	SZAJ 25-11	0138141	18	45	58	25	M6	30	M14	Steel	2.3
	186 - 266	332	SZAJ 25-12	0138142	18	45	58	25	M6	30	M14	Steel	2.5


Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB-J 123	0133103	18	50	62	106	15	26	30	30	M14	Steel	4.2

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	H-WBL 108	0130604	18	50	50	120	6	25	30	M14	Steel	5.4
	H-WB 105	0130122	18	50	80	108		24	30	M14	Steel	8.3
	H-WB 106	0132145	18	50	50	108		24	30	M14	Steel	5.2
	H-WBAL 100	0130504	18	50	60	108		24	30	M14	Aluminum	2.3

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 120	0146108	18	27.5	9.5	30	M14	M14 x 40	130



Technical advice and sales: Tel. +49-7133-103-2750