



SCHUNK chuck jaws for HO 7 MA 10


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	45 - 114	261	SZAJ 20-5	0138120	16	35	53	25	M6	25	M12	Steel	1.8
	73 - 142	261	SZAJ 20-6	0138125	16	35	53	25	M6	25	M12	Steel	1.6
	103 - 172	261	SZAJ 20-7	0138122	16	40	53	25	M6	25	M12	Steel	1.7
	133 - 203	261	SZAJ 20-8	0138127	16	40	53	25	M6	25	M12	Steel	1.6



Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB-J 102	0131109	16	35	42	83	15	19	25	25	M12	Steel	1.5

Jaw blanks

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/piece [kg]
	JBM 100	0114412	16	40	80	120	13	30	M12	Steel	3
	JBM 101	0114410	16	40	60	90	13	30	M12	Steel	1.6
	JBM 102	0114411	16	40	60	110	13	30	M12	Steel	2.1
	JBM 103	0114413	16	40	100	110	13	30	M12	Steel	3.4
	JBM 104	0114414	16	50	120	110	13	30	M12	Steel	5
	JBM 105	0114415	16	60	60	95	13	30	M12	Steel	2.7
	JBM 106	0114416	16	60	90	95	13	30	M12	Steel	4
	JBM 107	0114417	16	80	60	95	13	30	M12	Steel	3.5

Serrated bars



	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	JBM-ST 160	0114530	16	40	80	420	Steel	10.2
	JBM-ST 161	0114531	16	40	120	420	Steel	15.4
	JBM-ST 162	0114532	16	60	60	420	Steel	11.4
	JBM-STA 160	0114533	16	40	80	420	Aluminum	3.7




Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for HO 7 MA 10

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	H-WBL 82	0130602	16	40	40	102	4	20	25	M12	Steel	3
	H-WB 82	0130120	16	40	60	86		20	25	M12	Steel	4.1
	H-WB 84	0132146	16	40	40	85		20	25	M12	Steel	2.6
	H-WBAL 81	0130503	16	40	60	90		20	25	M12	Aluminum	1.5

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 101	0146107	16	26.5	8.5	25	M12	M12 x 35	70



Technical advice and sales: Tel. +49-7133-103-2750