


SCHUNK chuck jaws for HO 7 MA 6



Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	13 - 38	176	SZAJ-ST 16-2	0175501	12	30	40	34	20	M10	Steel	1.1


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	28 - 56	176	SZAJ 16-6	0176100	12	30	47	20	M6	20	M10	Steel	1.2
	56 - 88	176	SZAJ 16-8	0176102	12	30	47	20	M6	20	M10	Steel	1.1
	86 - 118	176	SZAJ 16-10	0176104	12	40	47	20	M6	20	M10	Steel	1.2


Full Grip Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KMWB-SM 165	0132700	12	120	50	160	50	40	60	25	20	M10	Steel	4.9
	KMWB-SA 165	0132800	12	120	40	165	58	48	59.5	25	20	M10	Aluminum	2.2

Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB-J 60	0133100	12	28	36	67	12	14	20	20	M10	Steel	0.8

Jaw blanks

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/piece [kg]
	SBMJ 70	0132150	12	35	60	80	12	20	M10	Steel	1.3






Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for HO 7 MA 6


Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	JBM-ST 120	0114510	12	35	60	420	Steel	6.7
	JBM-STA 120	0114511	12	40	60	420	Aluminum	2.8

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KM-WBL 60	0132600	12	32	32	82	4	15	20	M10	Steel	1.5
	KM-WBL 62	0132606	12	35	60	82	4	15	20	M10	Steel	3.6
	KM-WB 61	0130128	12	35	60	72		15	20	M10	Steel	2.9
	KM-WB 66	0132138	12	32	32	72		15	20	M10	Steel	1.4
	KM-WBAL 70	0132521	12	35	50	72		15	20	M10	Aluminum	0.9

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 61	0146100	12	22	7	20	M10	M10 x 25	50



Technical advice and sales: Tel. +49-7133-103-2750