





SCHUNK Spannbacken für HO 15 M 12


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB-J 123	0133103	18	50	62	106	15	26	30	30	M14	Stahl	4.2

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	H-WBL 108	0130604	18	50	50	120	6	25	30	M14	Stahl	5.4
	H-WB 105	0130122	18	50	80	108		24	30	M14	Stahl	8.3
	H-WB 106	0132145	18	50	50	108		24	30	M14	Stahl	5.2
	H-WBAL 100	0130504	18	50	60	108		24	30	M14	Aluminium	2.3

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmo- ment [Nm]
	NJ 120	0146108	18	27.5	9.5	30	M14	M14 x 40	130



Technische Beratung und Verkauf: Tel. +49-7133-103-2750