


# SCHUNK Spannbacken für HO 24 M 8


## Backenrohlinge

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Stück<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------------|
|  | JBM 100     | 0114412    | 16        | 40        | 80        | 120       | 13        | 30        | M12       | Stahl     | 3               |
|                                                                                   | JBM 101     | 0114410    | 16        | 40        | 60        | 90        | 13        | 30        | M12       | Stahl     | 1.6             |
|                                                                                   | JBM 102     | 0114411    | 16        | 40        | 60        | 110       | 13        | 30        | M12       | Stahl     | 2.1             |
|                                                                                   | JBM 103     | 0114413    | 16        | 40        | 100       | 110       | 13        | 30        | M12       | Stahl     | 3.4             |
|                                                                                   | JBM 104     | 0114414    | 16        | 50        | 120       | 110       | 13        | 30        | M12       | Stahl     | 5               |
|                                                                                   | JBM 105     | 0114415    | 16        | 60        | 60        | 95        | 13        | 30        | M12       | Stahl     | 2.7             |
|                                                                                   | JBM 106     | 0114416    | 16        | 60        | 90        | 95        | 13        | 30        | M12       | Stahl     | 4               |
|                                                                                   | JBM 107     | 0114417    | 16        | 80        | 60        | 95        | 13        | 30        | M12       | Stahl     | 3.5             |



## Harte Stufenaufsatzbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SHB-J 102   | 0131109    | 16        | 35        | 42        | 83        | 15        | 19        | 25        | 25        | M12       | Stahl     | 1.5            |

## Krallenbacken für Außenspannung

|                                                                                    | Spannbereich<br>ØD | Schwingkreis<br>SDmax | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | G  | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|------------------------------------------------------------------------------------|--------------------|-----------------------|-------------|------------|-----------|-----------|-----------|-----------|----|-----------|-----------|-----------|----------------|
|  | 31 - 73            | 220                   | SZAJ 20-5   | 0138120    | 16        | 35        | 53        | 25        | M6 | 25        | M12       | Stahl     | 1.8            |
|                                                                                    | 58 - 101           | 220                   | SZAJ 20-6   | 0138125    | 16        | 35        | 53        | 25        | M6 | 25        | M12       | Stahl     | 1.6            |
|                                                                                    | 88 - 131           | 220                   | SZAJ 20-7   | 0138122    | 16        | 40        | 53        | 25        | M6 | 25        | M12       | Stahl     | 1.7            |
|                                                                                    | 118 - 164          | 220                   | SZAJ 20-8   | 0138127    | 16        | 40        | 53        | 25        | M6 | 25        | M12       | Stahl     | 1.6            |

## Verzahnte Stangen



|                                                                                     | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Werkstoff | m/Stück<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------------|
|  | JBM-ST 160  | 0114530    | 16        | 40        | 80        | 420       | Stahl     | 10.2            |
|                                                                                     | JBM-ST 161  | 0114531    | 16        | 40        | 120       | 420       | Stahl     | 15.4            |
|                                                                                     | JBM-ST 162  | 0114532    | 16        | 60        | 60        | 420       | Stahl     | 11.4            |
|  | JBM-STA 160 | 0114533    | 16        | 40        | 80        | 420       | Aluminium | 3.7             |




Technische Beratung und Verkauf: Tel. +49-7133-103-2750

# SCHUNK Spannbacken für HO 24 M 8

## Weiche Aufsatzbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a1<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|------------|-----------|-----------|-----------|-----------|----------------|
|  | H-WBL 82    | 0130602    | 16        | 40        | 40        | 102       | 4          | 20        | 25        | M12       | Stahl     | 3              |
|                                                                                   | H-WB 82     | 0130120    | 16        | 40        | 60        | 86        |            | 20        | 25        | M12       | Stahl     | 4.1            |
|                                                                                   | H-WB 84     | 0132146    | 16        | 40        | 40        | 85        |            | 20        | 25        | M12       | Stahl     | 2.6            |
|  | H-WBAL 81   | 0130503    | 16        | 40        | 60        | 90        |            | 20        | 25        | M12       | Aluminium | 1.5            |

## Nutenstein

|                                                                                    | Bezeichnung | Ident.-Nr. | S<br>[mm] | H<br>[mm] | H1<br>[mm] | b<br>[mm] | G   | Zyl.-Schraube | Max. zul.<br>Anziehdrehmo-<br>ment<br>[Nm] |
|------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|------------|-----------|-----|---------------|--------------------------------------------|
|  | NJ 101      | 0146107    | 16        | 26.5      | 8.5        | 25        | M12 | M12 x 35      | 70                                         |



Technische Beratung und Verkauf: Tel. +49-7133-103-2750