



# SCHUNK chuck jaws for H0 27 M 8


## Claw jaws for O.D. clamping

|                                                                                   | Clamping range ØD | Swing diameter SDmax | Description | ID      | N [mm] | B [mm] | H [mm] | T [mm] | G  | b [mm] | Screws | Material | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------------|----------------------|-------------|---------|--------|--------|--------|--------|----|--------|--------|----------|------------|
|  | 30 - 68           | 215                  | SZAJ 20-5   | 0138120 | 16     | 35     | 53     | 25     | M6 | 25     | M12    | Steel    | 1.8        |
|                                                                                   | 49 - 96           | 215                  | SZAJ 20-6   | 0138125 | 16     | 35     | 53     | 25     | M6 | 25     | M12    | Steel    | 1.6        |
|                                                                                   | 79 - 126          | 215                  | SZAJ 20-7   | 0138122 | 16     | 40     | 53     | 25     | M6 | 25     | M12    | Steel    | 1.7        |
|                                                                                   | 109 - 156         | 215                  | SZAJ 20-8   | 0138127 | 16     | 40     | 53     | 25     | M6 | 25     | M12    | Steel    | 1.6        |



## Hard Stepped Top Jaws

|                                                                                   | Description | ID      | N [mm] | B [mm] | H [mm] | L [mm] | T [mm] | a [mm] | b [mm] | c [mm] | Screws | Material | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|----------|------------|
|  | SHB-J 102   | 0131109 | 16     | 35     | 42     | 83     | 15     | 19     | 25     | 25     | M12    | Steel    | 1.5        |

## Jaw blanks

|                                                                                    | Description | ID      | N [mm] | B [mm] | H [mm] | L [mm] | a [mm] | b [mm] | Screws | Material | m/piece [kg] |
|------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|--------|--------|--------|----------|--------------|
|  | JBM 100     | 0114412 | 16     | 40     | 80     | 120    | 13     | 30     | M12    | Steel    | 3            |
|                                                                                    | JBM 101     | 0114410 | 16     | 40     | 60     | 90     | 13     | 30     | M12    | Steel    | 1.6          |
|                                                                                    | JBM 102     | 0114411 | 16     | 40     | 60     | 110    | 13     | 30     | M12    | Steel    | 2.1          |
|                                                                                    | JBM 103     | 0114413 | 16     | 40     | 100    | 110    | 13     | 30     | M12    | Steel    | 3.4          |
|                                                                                    | JBM 104     | 0114414 | 16     | 50     | 120    | 110    | 13     | 30     | M12    | Steel    | 5            |
|                                                                                    | JBM 105     | 0114415 | 16     | 60     | 60     | 95     | 13     | 30     | M12    | Steel    | 2.7          |
|                                                                                    | JBM 106     | 0114416 | 16     | 60     | 90     | 95     | 13     | 30     | M12    | Steel    | 4            |
|                                                                                    | JBM 107     | 0114417 | 16     | 80     | 60     | 95     | 13     | 30     | M12    | Steel    | 3.5          |

## Serrated bars



|                                                                                     | Description | ID      | N [mm] | B [mm] | H [mm] | L [mm] | Material | m/piece [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|----------|--------------|
|  | JBM-ST 160  | 0114530 | 16     | 40     | 80     | 420    | Steel    | 10.2         |
|                                                                                     | JBM-ST 161  | 0114531 | 16     | 40     | 120    | 420    | Steel    | 15.4         |
|                                                                                     | JBM-ST 162  | 0114532 | 16     | 60     | 60     | 420    | Steel    | 11.4         |
|  | JBM-STA 160 | 0114533 | 16     | 40     | 80     | 420    | Aluminum | 3.7          |




Technical advice and sales: Tel. +49-7133-103-2750

# SCHUNK chuck jaws for H0 27 M 8

## Soft Top Jaws

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a1<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|-----------|-----------|--------|----------|---------------|
|  | H-WBL 82    | 0130602 | 16        | 40        | 40        | 102       | 4          | 20        | 25        | M12    | Steel    | 3             |
|                                                                                   | H-WB 82     | 0130120 | 16        | 40        | 60        | 86        |            | 20        | 25        | M12    | Steel    | 4.1           |
|                                                                                   | H-WB 84     | 0132146 | 16        | 40        | 40        | 85        |            | 20        | 25        | M12    | Steel    | 2.6           |
|  | H-WBAL 81   | 0130503 | 16        | 40        | 60        | 90        |            | 20        | 25        | M12    | Aluminum | 1.5           |

## T-nut

|                                                                                    | Description | ID      | S<br>[mm] | H<br>[mm] | H1<br>[mm] | b<br>[mm] | G   | Cyl.-screw | Max. adm.<br>tightening<br>torque<br>[Nm] |
|------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----------|-----|------------|-------------------------------------------|
|  | NJ 101      | 0146107 | 16        | 26.5      | 8.5        | 25        | M12 | M12 x 35   | 70                                        |



Technical advice and sales: Tel. +49-7133-103-2750