



# SCHUNK chuck jaws for H0 37 M 10




## Claw jaws for O.D. clamping

|                                                                                   | Clamping range ØD | Swing diameter SDmax | Description | ID      | N [mm] | B [mm] | H [mm] | T [mm] | G  | b [mm] | Screws | Material | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------------|----------------------|-------------|---------|--------|--------|--------|--------|----|--------|--------|----------|------------|
|  | 41 - 85           | 263                  | SZAJ 25-9   | 0138115 | 18     | 40     | 58     | 25     | M6 | 30     | M14    | Steel    | 2.7        |
|                                                                                   | 83 - 128          | 263                  | SZAJ 25-10  | 0138129 | 18     | 40     | 58     | 25     | M6 | 30     | M14    | Steel    | 2.3        |
|                                                                                   | 124 - 170         | 265                  | SZAJ 25-11  | 0138141 | 18     | 45     | 58     | 25     | M6 | 30     | M14    | Steel    | 2.3        |
|                                                                                   | 171 - 217         | 283                  | SZAJ 25-12  | 0138142 | 18     | 45     | 58     | 25     | M6 | 30     | M14    | Steel    | 2.5        |


## Hard Stepped Top Jaws

|                                                                                   | Description | ID      | N [mm] | B [mm] | H [mm] | L [mm] | T [mm] | a [mm] | b [mm] | c [mm] | Screws | Material | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|----------|------------|
|  | SHB-J 123   | 0133103 | 18     | 50     | 62     | 106    | 15     | 26     | 30     | 30     | M14    | Steel    | 4.2        |

## Soft Top Jaws

|                                                                                     | Description | ID      | N [mm] | B [mm] | H [mm] | L [mm] | a1 [mm] | a [mm] | b [mm] | Screws | Material | m/set [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|---------|--------|--------|--------|----------|------------|
|   | H-WBL 108   | 0130604 | 18     | 50     | 50     | 120    | 6       | 25     | 30     | M14    | Steel    | 5.4        |
|  | H-WB 105    | 0130122 | 18     | 50     | 80     | 108    |         | 24     | 30     | M14    | Steel    | 8.3        |
|                                                                                     | H-WB 106    | 0132145 | 18     | 50     | 50     | 108    |         | 24     | 30     | M14    | Steel    | 5.2        |
|  | H-WBAL 100  | 0130504 | 18     | 50     | 60     | 108    |         | 24     | 30     | M14    | Aluminum | 2.3        |

## T-nut

|                                                                                     | Description | ID      | S [mm] | H [mm] | H1 [mm] | b [mm] | G   | Cyl.-screw | Max. adm. tightening torque [Nm] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|---------|--------|-----|------------|----------------------------------|
|  | NJ 120      | 0146108 | 18     | 27.5   | 9.5     | 30     | M14 | M14 x 40   | 130                              |



Technical advice and sales: Tel. +49-7133-103-2750