





SCHUNK chuck jaws for AS210


Full Grip Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KMWB-SM 210	0132701	14	140	70	200	60	50	70	30	25	M12	Steel	8.8
	KMWB-SM 211	0132705	14	140	70	200	80	70	70	30	25	M12	Steel	11.7
	KMWB-SA 210	0132801	14	140	50	200	58	48	72.5	35	25	M12	Aluminum	3.3
	KMWB-SA 211	0132805	14	140	50	200	80	70	72.5	35	25	M12	Aluminum	4.5

Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB-J 80	0133109	14	35	51	87	12	15.5	25	25	M12	Steel	1.85
	SHB-J 82	0133110	14	32	38	79	12	16	25	25	M12	Steel	1.2

Jaw blanks





	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/piece [kg]
	JBM 80	0114404	14	40	80	95	13	25	M12	Steel	2.4
	JBM 81	0114400	14	40	40	70	13	25	M12	Steel	0.9
	JBM 82	0114401	14	40	40	95	13	25	M12	Steel	1.2
	JBM 83	0114402	14	40	60	70	13	25	M12	Steel	1.3
	JBM 84	0114403	14	40	60	95	13	25	M12	Steel	1.7
	JBM 85	0114405	14	40	100	95	13	25	M12	Steel	2.9
	JBM 86	0114406	14	60	60	70	13	25	M12	Steel	2
	JBM 87	0114407	14	80	60	70	13	25	M12	Steel	2.6





Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for AS210

QUENTES fiberglass jaws

	Clamping range ØD	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Max. tightening torque [Nm]	Screws	m/set [kg]
	20 - 65	TRQJ 200-1	0150005	14	40	55	76	25		M12	0.77
	98 - 167	TRQJ 200-2	0150006	14	40	64	82	25		M12	1
		QUENTES 10-3	0150100						8		
		QUENTES 20-3	0150200						8		

Serrated bars




	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	JBM-ST 140	0114520	14	40	80	420	Steel	10.2
	JBM-ST 141	0114521	14	60	60	420	Steel	11.2
	JBM-STA 140	0114522	14	40	80	420	Aluminum	3.7




Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for AS210

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KM-WBL 80	0132601	14	35	40	102	4	20	25	M12	Steel	2.7
	KM-WBL 81	0132607	14	40	80	102	4	20	25	M12	Steel	6
	KM-WBL 82	0132615	14	40	100	102	4	20	25	M12	Steel	7.6
	KM-WB 84	0132126	14	35	60	95		24	25	M12	Steel	3.9
	KM-WB 85	0132127	14	40	80	95		24	25	M12	Steel	6.1
	KM-WB 88	0132139	14	35	40	95		24	25	M12	Steel	2.7
	KM-WBAL 80	0132522	14	40	60	90		20	25	M12	Aluminum	1.5

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 80	0146101	14	24.5	8.5	25	M12	M12 x 35	70



Technical advice and sales: Tel. +49-7133-103-2750