




SCHUNK chuck jaws for AS165


Full Grip Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KMWB-SM 165	0132700	12	120	50	160	50	40	60	25	20	M10	Steel	4.9
	KMWB-SA 165	0132800	12	120	40	165	58	48	59.5	25	20	M10	Aluminum	2.2



Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB-J 60	0133100	12	28	36	67	12	14	20	20	M10	Steel	0.8

Jaw blanks

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/piece [kg]
	SBMJ 70	0132150	12	35	60	80	12	20	M10	Steel	1.3

QUENTES fiberglass jaws



	Clamping range ØD	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Max. tightening torque [Nm]	Screws	m/set [kg]
	20 - 47	TRQJ 160-1	0150022	12	40	55	65	20		M10	0.6
		QUENTES 10-3	0150100						8		








Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for AS165


Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	JBM-ST 120	0114510	12	35	60	420	Steel	6.7
	JBM-STA 120	0114511	12	40	60	420	Aluminum	2.8

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KM-WBL 60	0132600	12	32	32	82	4	15	20	M10	Steel	1.5
	KM-WBL 62	0132606	12	35	60	82	4	15	20	M10	Steel	3.6
	KM-WB 61	0130128	12	35	60	72		15	20	M10	Steel	2.9
	KM-WB 66	0132138	12	32	32	72		15	20	M10	Steel	1.4
	KM-WBAL 70	0132521	12	35	50	72		15	20	M10	Aluminum	0.9

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 61	0146100	12	22	7	20	M10	M10 x 25	50



Technical advice and sales: Tel. +49-7133-103-2750