



# SCHUNK chuck jaws for BB206



## Claw jaws For bar clamping

|                                                                                   | Clamping range ØD | Swing diameter SDmax | Description  | ID      | N [mm] | B [mm] | H [mm] | T [mm] | b [mm] | Screws | Material | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------------|----------------------|--------------|---------|--------|--------|--------|--------|--------|--------|----------|------------|
|  | 18 - 38           | 177                  | SZAJ-ST 16-2 | 0175501 | 12     | 30     | 40     | 34     | 20     | M10    | Steel    | 1.1        |


## Claw jaws for O.D. clamping

|                                                                                   | Clamping range ØD | Swing diameter SDmax | Description | ID      | N [mm] | B [mm] | H [mm] | T [mm] | G  | b [mm] | Screws | Material | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------------|----------------------|-------------|---------|--------|--------|--------|--------|----|--------|--------|----------|------------|
|  | 37 - 56           | 177                  | SZAJ 16-6   | 0176100 | 12     | 30     | 47     | 20     | M6 | 20     | M10    | Steel    | 1.2        |
|                                                                                   | 52 - 72           | 177                  | SZAJ 16-7   | 0176101 | 12     | 30     | 47     | 20     | M6 | 20     | M10    | Steel    | 1          |
|                                                                                   | 68 - 88           | 177                  | SZAJ 16-8   | 0176102 | 12     | 30     | 47     | 20     | M6 | 20     | M10    | Steel    | 1.1        |
|                                                                                   | 82 - 102          | 177                  | SZAJ 16-9   | 0176103 | 12     | 30     | 47     | 20     | M6 | 20     | M10    | Steel    | 1.1        |
|                                                                                   | 98 - 118          | 177                  | SZAJ 16-10  | 0176104 | 12     | 40     | 47     | 20     | M6 | 20     | M10    | Steel    | 1.2        |


## Full Grip Jaws

|                                                                                     | Description | ID      | N [mm] | B [mm] | B1 [mm] | Ø D [mm] | H [mm] | H1 [mm] | L [mm] | a [mm] | b [mm] | Screws | Material | m/set [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|---------|----------|--------|---------|--------|--------|--------|--------|----------|------------|
|   | KMWB-SM 165 | 0132700 | 12     | 120    | 50      | 160      | 50     | 40      | 60     | 25     | 20     | M10    | Steel    | 4.9        |
|  | KMWB-SA 165 | 0132800 | 12     | 120    | 40      | 165      | 58     | 48      | 59.5   | 25     | 20     | M10    | Aluminum | 2.2        |

## Hard Stepped Top Jaws

|                                                                                     | Description | ID      | N [mm] | B [mm] | H [mm] | L [mm] | T [mm] | a [mm] | b [mm] | c [mm] | Screws | Material | m/set [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|----------|------------|
|  | SHB-J 60    | 0133100 | 12     | 28     | 36     | 67     | 12     | 14     | 20     | 20     | M10    | Steel    | 0.8        |

## Jaw blanks



|                                                                                     | Description | ID      | N [mm] | B [mm] | H [mm] | L [mm] | a [mm] | b [mm] | Screws | Material | m/piece [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|--------|--------|--------|----------|--------------|
|  | SBMJ 70     | 0132150 | 12     | 35     | 60     | 80     | 12     | 20     | M10    | Steel    | 1.3          |








Technical advice and sales: Tel. +49-7133-103-2750

# SCHUNK chuck jaws for BB206


## Serrated bars

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Material | m/piece<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|----------|-----------------|
|  | JBM-ST 120  | 0114510 | 12        | 35        | 60        | 420       | Steel    | 6.7             |
|  | JBM-STA 120 | 0114511 | 12        | 40        | 60        | 420       | Aluminum | 2.8             |

## Soft Top Jaws

|                                                                                     | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a1<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|-----------|-----------|--------|----------|---------------|
|    | KM-WBL 60   | 0132600 | 12        | 32        | 32        | 82        | 4          | 15        | 20        | M10    | Steel    | 1.5           |
|    | KM-WBL 62   | 0132606 | 12        | 35        | 60        | 82        | 4          | 15        | 20        | M10    | Steel    | 3.6           |
|   | KM-WB 61    | 0130128 | 12        | 35        | 60        | 72        |            | 15        | 20        | M10    | Steel    | 2.9           |
|   | KM-WB 66    | 0132138 | 12        | 32        | 32        | 72        |            | 15        | 20        | M10    | Steel    | 1.4           |
|  | KM-WBAL 70  | 0132521 | 12        | 35        | 50        | 72        |            | 15        | 20        | M10    | Aluminum | 0.9           |

## T-nut

|                                                                                     | Description | ID      | S<br>[mm] | H<br>[mm] | H1<br>[mm] | b<br>[mm] | G   | Cyl.-screw | Max. adm. tightening torque<br>[Nm] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----------|-----|------------|-------------------------------------|
|  | NJ 62       | 0146133 | 12        | 18.5      | 7.5        | 20        | M10 | M10 x 25   | 50                                  |



Technical advice and sales: Tel. +49-7133-103-2750