




SCHUNK Spannbacken für BBT212


Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Stück [kg]
	JBM 120	0114420	21	50	60	130	15	30	M16	Stahl	3.1
	JBM 121	0114421	21	50	80	130	15	30	M16	Stahl	4.1
	JBM 122	0114422	21	50	120	130	15	30	M16	Stahl	6
	JBM 123	0114423	21	58	150	130	15	30	M16	Stahl	8.8
	JBM 124	0114424	21	80	80	130	15	30	M16	Stahl	6.2

Verzahnte Stangen

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	JBM-ST 210	0114540	21	50	80	420	Stahl	12.7
	JBM-ST 211	0114541	21	60	120	420	Stahl	23.2
	JBM-STA 210	0114542	21	50	80	420	Aluminium	4.6

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmo- ment [Nm]
	NJ 124	0146123	21	28	11.5	30	M16	M16 x 40	150



Technische Beratung und Verkauf: Tel. +49-7133-103-2750