




Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB-J 123	0133103	18	50	62	106	15	26	30	30	M14	Stahl	4.2


Krallenbacken für Außenspannung

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SZAJ 30-1	0138124	18	50	65	25	M8	30	M14	Stahl	3.8
	SZAJ 30-2	0138126	18	50	65	25	M8	30	M14	Stahl	4.1
	SZAJ 30-3	0138128	18	50	65	25	M8	30	M14	Stahl	3.4
	SZAJ 30-4	0138130	18	50	65	25	M8	30	M14	Stahl	4.8



Krallenbacken für Innenspannung

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SZIJ 30-9	0179122	18	50	65	25	M8	30	M14	Stahl	5
	SZIJ 30-10	0179124	18	50	65	25	M8	30	M14	Stahl	4.6
	SZIJ 30-11	0179126	18	50	65	25	M8	30	M14	Stahl	3.6
	SZIJ 30-12	0179127	18	50	65	25	M8	30	M14	Stahl	4.5

Pendelbacken




	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	PNS-M 315-18-1	0160210	68	35	2.4
	PNS-M 315-18-3	0160212	68	35	2.65

Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	KMWB-SM 300	0132703	18	240	120	300	70	55	110	40	30	M14	Stahl	26.6
	KMWB-SA 300	0132803	18	240	80	320	78	63	117	40	30	M14	Aluminium	10.5



Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	KM-WBL 120	0132603	18	50	50	145	10	30	30	M14	Stahl	7
	KM-WBL 123	0132617	18	50	100	145	10	30	30	M14	Stahl	14.5
	KM-WB 121	0132107	18	50	50	130		40	30	M14	Stahl	6.8
	KM-WB 123	0132109	18	50	80	130		40	30	M14	Stahl	10.5
	KM-WB 125	0132130	18	50	120	130		40	30	M14	Stahl	15.9
	KM-WBAL 120	0132524	18	50	80	130		40	30	M14	Aluminium	3.8

