



SCHUNK chuck jaws for DL12



Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	80 - 96	275	SZIJ 30-9	0179122	18	50	65	25	M8	30	M14	Steel	5
	126 - 156	282	SZIJ 30-10	0179124	18	50	65	25	M8	30	M14	Steel	4.6
	189 - 219	266	SZIJ 30-11	0179126	18	50	65	25	M8	30	M14	Steel	3.6
	241 - 272	318	SZIJ 30-12	0179127	18	50	65	25	M8	30	M14	Steel	4.5


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	93 - 123	262	SZAJ 25-10	0138129	18	40	58	25	M6	30	M14	Steel	2.3
	135 - 165	265	SZAJ 25-11	0138141	18	45	58	25	M6	30	M14	Steel	2.3
	182 - 213	284	SZAJ 25-12	0138142	18	45	58	25	M6	30	M14	Steel	2.5
	44 - 66	281	SZAJ 30-1	0138124	18	50	65	25	M8	30	M14	Steel	3.8
	96 - 126	292	SZAJ 30-2	0138126	18	50	65	25	M8	30	M14	Steel	4.1
	162 - 192	288	SZAJ 30-3	0138128	18	50	65	25	M8	30	M14	Steel	3.4
	226 - 256	331	SZAJ 30-4	0138130	18	50	65	25	M8	30	M14	Steel	4.8


Full Grip Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KMWB-SM 300	0132703	18	240	120	300	70	55	110	40	30	M14	Steel	26.6
	KMWB-SA 300	0132803	18	240	80	320	78	63	117	40	30	M14	Aluminum	10.5

Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB-J 123	0133103	18	50	62	106	15	26	30	30	M14	Steel	4.2

Pendulum jaws




	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	64 - 86	262	PNS-M 315-18-1	0160210	68	35	2.4
	140 - 163	280	PNS-M 315-18-3	0160212	68	35	2.65



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for DL12

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KM-WBL 120	0132603	18	50	50	145	10	30	30	M14	Steel	7
	KM-WBL 123	0132617	18	50	100	145	10	30	30	M14	Steel	14.5
	KM-WB 121	0132107	18	50	50	130		40	30	M14	Steel	6.8
	KM-WB 123	0132109	18	50	80	130		40	30	M14	Steel	10.5
	KM-WB 125	0132130	18	50	120	130		40	30	M14	Steel	15.9
	KM-WBAL 120	0132524	18	50	80	130		40	30	M14	Aluminum	3.8



Technical advice and sales: Tel. +49-7133-103-2750