



Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	KM-WB 211	0132114	25	80	80	195	50	60	M20	Stahl	26.3
	KM-WB 213	0132155	25	75	115	180	50	60	M20	Stahl	31.7
	KM-WB 214	0132200	25	75	155	180	50	60	M20	Stahl	42.9

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmo- ment [Nm]
	NJ 211	0146106	25	54	19	60	M20	M20 x 70	300

