



SCHUNK Spannbacken für H08



Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Stück [kg]
	JBM 80	0114404	14	40	80	95	13	25	M12	Stahl	2.4
	JBM 81	0114400	14	40	40	70	13	25	M12	Stahl	0.9
	JBM 82	0114401	14	40	40	95	13	25	M12	Stahl	1.2
	JBM 83	0114402	14	40	60	70	13	25	M12	Stahl	1.3
	JBM 84	0114403	14	40	60	95	13	25	M12	Stahl	1.7
	JBM 85	0114405	14	40	100	95	13	25	M12	Stahl	2.9
	JBM 86	0114406	14	60	60	70	13	25	M12	Stahl	2
	JBM 87	0114407	14	80	60	70	13	25	M12	Stahl	2.6



Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB-J 80	0133109	14	35	51	87	12	15.5	25	25	M12	Stahl	1.85
	SHB-J 82	0133110	14	32	38	79	12	16	25	25	M12	Stahl	1.2

Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	KMWB-SM 210	0132701	14	140	70	200	60	50	70	30	25	M12	Stahl	8.8
	KMWB-SM 211	0132705	14	140	70	200	80	70	70	30	25	M12	Stahl	11.7
	KMWB-SA 210	0132801	14	140	50	200	58	48	72.5	35	25	M12	Aluminium	3.3
	KMWB-SA 211	0132805	14	140	50	200	80	70	72.5	35	25	M12	Aluminium	4.5

Verzahnte Stangen




	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	JBM-ST 140	0114520	14	40	80	420	Stahl	10.2
	JBM-ST 141	0114521	14	60	60	420	Stahl	11.2
	JBM-STA 140	0114522	14	40	80	420	Aluminium	3.7




Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für H08

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	KM-WBL 80	0132601	14	35	40	102	4	20	25	M12	Stahl	2.7
	KM-WBL 81	0132607	14	40	80	102	4	20	25	M12	Stahl	6
	KM-WBL 82	0132615	14	40	100	102	4	20	25	M12	Stahl	7.6
	KM-WB 84	0132126	14	35	60	95		24	25	M12	Stahl	3.9
	KM-WB 85	0132127	14	40	80	95		24	25	M12	Stahl	6.1
	KM-WB 88	0132139	14	35	40	95		24	25	M12	Stahl	2.7
	KM-WBAL 80	0132522	14	40	60	90		20	25	M12	Aluminium	1.5

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmo- ment [Nm]
	NJ 80	0146101	14	24.5	8.5	25	M12	M12 x 35	70



Technische Beratung und Verkauf: Tel. +49-7133-103-2750