




# SCHUNK chuck jaws for HLA8-15




## Full Grip Jaws

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | B1<br>[mm] | Ø D<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-------------|-----------|------------|-----------|-----------|-----------|--------|----------|---------------|
|  | KMWB-SM 300 | 0132703 | 18        | 240       | 120        | 300         | 70        | 55         | 110       | 40        | 30        | M14    | Steel    | 26.6          |
|  | KMWB-SA 300 | 0132803 | 18        | 240       | 80         | 320         | 78        | 63         | 117       | 40        | 30        | M14    | Aluminum | 10.5          |

## Hard Stepped Top Jaws

|                                                                                   | Swing diameter<br>SDmax | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|---------------|
|  | 312                     | SHB-J 123   | 0133103 | 18        | 50        | 62        | 106       | 15        | 26        | 30        | 30        | M14    | Steel    | 4.2           |

## Soft Top Jaws

|                                                                                     | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a1<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|-----------|-----------|--------|----------|---------------|
|  | KM-WBL 120  | 0132603 | 18        | 50        | 50        | 145       | 10         | 30        | 30        | M14    | Steel    | 7             |
|                                                                                     | KM-WBL 123  | 0132617 | 18        | 50        | 100       | 145       | 10         | 30        | 30        | M14    | Steel    | 14.5          |
|  | KM-WB 121   | 0132107 | 18        | 50        | 50        | 130       |            | 40        | 30        | M14    | Steel    | 6.8           |
|                                                                                     | KM-WB 123   | 0132109 | 18        | 50        | 80        | 130       |            | 40        | 30        | M14    | Steel    | 10.5          |
|                                                                                     | KM-WB 125   | 0132130 | 18        | 50        | 120       | 130       |            | 40        | 30        | M14    | Steel    | 15.9          |
|  | KM-WBAL 120 | 0132524 | 18        | 50        | 80        | 130       |            | 40        | 30        | M14    | Aluminum | 3.8           |



Technical advice and sales: Tel. +49-7133-103-2750