




# SCHUNK chuck jaws for HOB18





## Hard Stepped Top Jaws

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|---------------|
|  | SHB-J 150   | 0133114 | 22        | 60        | 86        | 143       | 20        | 27        | 43        | 43        | M20    | Steel    | 9             |


## Serrated bars

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Material | m/piece<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|----------|-----------------|
|  | JBM-ST 220  | 0114550 | 22        | 60        | 120       | 420       | Steel    | 23.2            |
|  | JBM-STA 220 | 0114552 | 22        | 60        | 100       | 420       | Aluminum | 7               |

## Soft Top Jaws

|                                                                                     | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a1<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|-----------|-----------|--------|----------|---------------|
|  | KM-WBL 150  | 0132605 | 22        | 60        | 60        | 185       | 10         | 30        | 43        | M20    | Steel    | 12.6          |
|  | KM-WB 153   | 0132132 | 22        | 60        | 80        | 165       |            | 37        | 43        | M20    | Steel    | 16.1          |
|  | KM-WB 155   | 0132156 | 22        | 60        | 120       | 165       |            | 37        | 43        | M20    | Steel    | 24.2          |
|  | KM-WBAL 150 | 0132526 | 22        | 60        | 80        | 145       |            | 30        | 43        | M20    | Aluminum | 5.1           |

## T-nut

|                                                                                     | Description | ID      | S<br>[mm] | S1<br>[mm] | H<br>[mm] | H1<br>[mm] | b<br>[mm] | G   | Cyl.-screw | Max. adm. tightening torque<br>[Nm] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|------------|-----------|------------|-----------|-----|------------|-------------------------------------|
|  | NJ 152      | 0146125 | 24        | 22         | 45.5      | 16.5       | 43        | M20 | M20 x 60   | 300                                 |



Technical advice and sales: Tel. +49-7133-103-2750