




# SCHUNK chuck jaws for HOB06


## Full Grip Jaws

|                                                                                   | Description    | ID      | N<br>[mm] | B<br>[mm] | B1<br>[mm] | Ø D<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|----------------|---------|-----------|-----------|------------|-------------|-----------|------------|-----------|-----------|-----------|--------|----------|---------------|
|  | KMWB-SM<br>165 | 0132700 | 12        | 120       | 50         | 160         | 50        | 40         | 60        | 25        | 20        | M10    | Steel    | 4.9           |
|  | KMWB-SA<br>165 | 0132800 | 12        | 120       | 40         | 165         | 58        | 48         | 59.5      | 25        | 20        | M10    | Aluminum | 2.2           |



## Hard Stepped Top Jaws

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|---------------|
|  | SHB-J 60    | 0133100 | 12        | 28        | 36        | 67        | 12        | 14        | 20        | 20        | M10    | Steel    | 0.8           |

## Jaw blanks

|                                                                                     | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/piece<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|-----------------|
|  | SBMJ 70     | 0132150 | 12        | 35        | 60        | 80        | 12        | 20        | M10    | Steel    | 1.3             |

## QUENTES fiberglass jaws



|                                                                                     | Clamping<br>range ØD | Description  | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | b<br>[mm] | Max.<br>tightening<br>torque<br>[Nm] | Screws | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|----------------------|--------------|---------|-----------|-----------|-----------|-----------|-----------|--------------------------------------|--------|---------------|
|  | 20 - 47              | TRQJ 160-1   | 0150022 | 12        | 40        | 55        | 65        | 20        |                                      | M10    | 0.6           |
|  |                      | QUENTES 10-3 | 0150100 |           |           |           |           |           | 8                                    |        |               |






Technical advice and sales: Tel. +49-7133-103-2750

# SCHUNK chuck jaws for HOB06


## Serrated bars

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Material | m/piece<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|----------|-----------------|
|  | JBM-ST 120  | 0114510 | 12        | 35        | 60        | 420       | Steel    | 6.7             |
|  | JBM-STA 120 | 0114511 | 12        | 40        | 60        | 420       | Aluminum | 2.8             |

## Soft Top Jaws

|                                                                                     | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a1<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|-----------|-----------|--------|----------|---------------|
|    | KM-WBL 60   | 0132600 | 12        | 32        | 32        | 82        | 4          | 15        | 20        | M10    | Steel    | 1.5           |
|                                                                                     | KM-WBL 62   | 0132606 | 12        | 35        | 60        | 82        | 4          | 15        | 20        | M10    | Steel    | 3.6           |
|   | KM-WB 61    | 0130128 | 12        | 35        | 60        | 72        |            | 15        | 20        | M10    | Steel    | 2.9           |
|                                                                                     | KM-WB 66    | 0132138 | 12        | 32        | 32        | 72        |            | 15        | 20        | M10    | Steel    | 1.4           |
|  | KM-WBAL 70  | 0132521 | 12        | 35        | 50        | 72        |            | 15        | 20        | M10    | Aluminum | 0.9           |

## T-nut

|                                                                                     | Description | ID      | S<br>[mm] | H<br>[mm] | H1<br>[mm] | b<br>[mm] | G   | Cyl.-screw | Max. adm. tightening torque<br>[Nm] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----------|-----|------------|-------------------------------------|
|  | NJ 61       | 0146100 | 12        | 22        | 7          | 20        | M10 | M10 x 25   | 50                                  |



Technical advice and sales: Tel. +49-7133-103-2750