



SCHUNK chuck jaws for HOB04

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KM-WB 44	0132101	8	20	40	48	4	8	15	M6	Steel	0.7

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 42	0146129	8	13.5	4.5	15	M6	M6 x 18	16



Technical advice and sales: Tel. +49-7133-103-2750