




SCHUNK chuck jaws for HOH300




Full Grip Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KMWB-SM 300	0132703	18	240	120	300	70	55	110	40	30	M14	Steel	26.6
	KMWB-SA 300	0132803	18	240	80	320	78	63	117	40	30	M14	Aluminum	10.5


Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB-J 123	0133103	18	50	62	106	15	26	30	30	M14	Steel	4.2

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KM-WBL 120	0132603	18	50	50	145	10	30	30	M14	Steel	7
	KM-WBL 123	0132617	18	50	100	145	10	30	30	M14	Steel	14.5
	KM-WB 121	0132107	18	50	50	130		40	30	M14	Steel	6.8
	KM-WB 123	0132109	18	50	80	130		40	30	M14	Steel	10.5
	KM-WB 125	0132130	18	50	120	130		40	30	M14	Steel	15.9
	KM-WBAL 120	0132524	18	50	80	130		40	30	M14	Aluminum	3.8

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 121	0146103	18	33.5	13.5	30	M14	M14 x 45	130



Technical advice and sales: Tel. +49-7133-103-2750