



SCHUNK chuck jaws for N12


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	20 - 89	312	SZAJ-ST 30-1	0175510	18	50	50	43	30	M14	Steel	3.5



Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	80 - 93	272	SZIJ 30-9	0179122	18	50	65	25	M8	30	M14	Steel	5
	131 - 154	279	SZIJ 30-10	0179124	18	50	65	25	M8	30	M14	Steel	4.6
	193 - 217	263	SZIJ 30-11	0179126	18	50	65	25	M8	30	M14	Steel	3.6
	246 - 270	316	SZIJ 30-12	0179127	18	50	65	25	M8	30	M14	Steel	4.5


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	98 - 121	260	SZAJ 25-10	0138129	18	40	58	25	M6	30	M14	Steel	2.3
	140 - 163	263	SZAJ 25-11	0138141	18	45	58	25	M6	30	M14	Steel	2.3
	187 - 210	281	SZAJ 25-12	0138142	18	45	58	25	M6	30	M14	Steel	2.5
	44 - 63	278	SZAJ 30-1	0138124	18	50	65	25	M8	30	M14	Steel	3.8
	101 - 123	290	SZAJ 30-2	0138126	18	50	65	25	M8	30	M14	Steel	4.1
	166 - 190	285	SZAJ 30-3	0138128	18	50	65	25	M8	30	M14	Steel	3.4
	230 - 254	328	SZAJ 30-4	0138130	18	50	65	25	M8	30	M14	Steel	4.8

Full Grip Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KMWB-SM 300	0132703	18	240	120	300	70	55	110	40	30	M14	Steel	26.6
	KMWB-SA 300	0132803	18	240	80	320	78	63	117	40	30	M14	Aluminum	10.5

Hard Stepped Top Jaws


	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB-J 123	0133103	18	50	62	106	15	26	30	30	M14	Steel	4.2






Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for N12


Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	68 - 112	291	PNS-M 315-18-1	0160210	68	35	2.4
	105 - 144	312	PNS-M 315-18-2	0160211	68	35	2.45
	146 - 202	330	PNS-M 315-18-3	0160212	68	35	2.65
	163 - 213	332	PNS-M 315-18-4	0160213	68	35	3

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KM-WBL 120	0132603	18	50	50	145	10	30	30	M14	Steel	7
	KM-WBL 123	0132617	18	50	100	145	10	30	30	M14	Steel	14.5
	KM-WB 121	0132107	18	50	50	130		40	30	M14	Steel	6.8
	KM-WB 123	0132109	18	50	80	130		40	30	M14	Steel	10.5
	KM-WB 125	0132130	18	50	120	130		40	30	M14	Steel	15.9
	KM-WBAL 120	0132524	18	50	80	130		40	30	M14	Aluminum	3.8

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 121	0146103	18	33.5	13.5	30	M14	M14 x 45	130
	NJ 121 gesägt/sawn	0146001	18	33.5	13.5		M14	M14 x 45	130



Technical advice and sales: Tel. +49-7133-103-2750