



# SCHUNK chuck jaws for N04


## Jaw blanks

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/piece<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|-----------------|
|  | SBMJ 50     | 0132149 | 10        | 22        | 47        | 55        | 8         | 14        | M8     | Steel    | 0.4             |


## Serrated bars

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Material | m/piece<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|----------|-----------------|
|  | JBm-ST 100  | 0114500 | 10        | 32        | 32        | 420       | Steel    | 3.1             |
|  | JBm-STA 100 | 0114501 | 10        | 30        | 40        | 420       | Aluminum | 1.3             |

## Soft Top Jaws

|                                                                                     | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a1<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|-----------|-----------|--------|----------|---------------|
|  | KM-WB 45    | 0132102 | 10        | 25        | 32        | 55        | 4          | 13        | 14        | M8     | Steel    | 0.8           |
|                                                                                     | KM-WB 46    | 0132103 | 10        | 22        | 47        | 55        | 4          | 13        | 14        | M8     | Steel    | 1             |

## T-nut

|                                                                                     | Description | ID      | S<br>[mm] | H<br>[mm] | H1<br>[mm] | b<br>[mm] | G  | Cyl.-screw | Max. adm. tightening torque<br>[Nm] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----------|----|------------|-------------------------------------|
|  | NJ 41       | 0146116 | 10        | 18        | 5.5        | 14        | M8 | M8 x 22    | 30                                  |



Technical advice and sales: Tel. +49-7133-103-2750