




SCHUNK Spannbacken für NLT08


Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Stück [kg]
	JBM 80	0114404	14	40	80	95	13	25	M12	Stahl	2.4
	JBM 81	0114400	14	40	40	70	13	25	M12	Stahl	0.9
	JBM 82	0114401	14	40	40	95	13	25	M12	Stahl	1.2
	JBM 83	0114402	14	40	60	70	13	25	M12	Stahl	1.3
	JBM 84	0114403	14	40	60	95	13	25	M12	Stahl	1.7
	JBM 85	0114405	14	40	100	95	13	25	M12	Stahl	2.9
	JBM 86	0114406	14	60	60	70	13	25	M12	Stahl	2
	JBM 87	0114407	14	80	60	70	13	25	M12	Stahl	2.6

Verzahnte Stangen

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	JBM-ST 140	0114520	14	40	80	420	Stahl	10.2
	JBM-ST 141	0114521	14	60	60	420	Stahl	11.2
	JBM-STA 140	0114522	14	40	80	420	Aluminium	3.7

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmo- ment [Nm]
	NJ 80	0146101	14	24.5	8.5	25	M12	M12 x 35	70



Technische Beratung und Verkauf: Tel. +49-7133-103-2750