



SCHUNK chuck jaws for NV18


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	156 - 217	450	SZIJ 38-1	0179132	22	60	85	33	M8	43	M20	Steel	9.5
	212 - 273	450	SZIJ 38-2	0179133	22	60	85	33	M8	43	M20	Steel	9.1
	267 - 329	442	SZIJ 38-3	0179134	22	60	85	33	M8	43	M20	Steel	7.6
	337 - 399	452	SZIJ 38-4	0179135	22	60	85	33	M8	43	M20	Steel	7.1
	397 - 459	502	SZIJ 38-5	0179136	22	60	85	33	M8	43	M20	Steel	8.6


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	101 - 162	446	SZAJ 38-1	0138135	22	60	85	33	M8	43	M20	Steel	10.2
	157 - 220	452	SZAJ 38-2	0138136	22	60	85	33	M8	43	M20	Steel	9
	219 - 280	452	SZAJ 38-3	0138137	22	60	85	33	M8	43	M20	Steel	7.5
	280 - 342	473	SZAJ 38-4	0138138	22	60	85	33	M8	43	M20	Steel	7.5
	340 - 402	489	SZAJ 38-5	0138139	22	60	85	33	M8	43	M20	Steel	8.2
	400 - 450	529	SZAJ 38-6	0138140	22	60	85	33	M8	43	M20	Steel	9.5

Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB-J 150	0133114	22	60	86	143	20	27	43	43	M20	Steel	9

Serrated bars



	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	JBM-ST 220	0114550	22	60	120	420	Steel	23.2
	JBM-STA 220	0114552	22	60	100	420	Aluminum	7




Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for NV18

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KM-WBL 150	0132605	22	60	60	185	10	30	43	M20	Steel	12.6
	KM-WB 153	0132132	22	60	80	165		37	43	M20	Steel	16.1
	KM-WB 155	0132156	22	60	120	165		37	43	M20	Steel	24.2
	KM-WBAL 150	0132526	22	60	80	145		30	43	M20	Aluminum	5.1

T-nut

	Description	ID	S [mm]	S1 [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 212	0146138	25.5	22	39.5	19	43	M20	M20 x 50	300



Technical advice and sales: Tel. +49-7133-103-2750