




# SCHUNK Spannbacken für QJR08



## Backenrohlinge

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Min. Abstand<br>a (Backen-<br>spitze bis<br>erste<br>Bohrung)<br>[mm] | Min. Abstand<br>b (Erste bis<br>zweite<br>Bohrung)<br>[mm] | Schrauben | Werkstoff | m/Stück<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------------------------------------------------------------------|------------------------------------------------------------|-----------|-----------|-----------------|
|  | JBM 80      | 0114404    | 14        | 40        | 80        | 95        | 13                                                                    | 25                                                         | M12       | Stahl     | 2.4             |
|                                                                                   | JBM 81      | 0114400    | 14        | 40        | 40        | 70        | 13                                                                    | 25                                                         | M12       | Stahl     | 0.9             |
|                                                                                   | JBM 82      | 0114401    | 14        | 40        | 40        | 95        | 13                                                                    | 25                                                         | M12       | Stahl     | 1.2             |
|                                                                                   | JBM 83      | 0114402    | 14        | 40        | 60        | 70        | 13                                                                    | 25                                                         | M12       | Stahl     | 1.3             |
|                                                                                   | JBM 84      | 0114403    | 14        | 40        | 60        | 95        | 13                                                                    | 25                                                         | M12       | Stahl     | 1.7             |
|                                                                                   | JBM 85      | 0114405    | 14        | 40        | 100       | 95        | 13                                                                    | 25                                                         | M12       | Stahl     | 2.9             |
|                                                                                   | JBM 86      | 0114406    | 14        | 60        | 60        | 70        | 13                                                                    | 25                                                         | M12       | Stahl     | 2               |
|                                                                                   | JBM 87      | 0114407    | 14        | 80        | 60        | 70        | 13                                                                    | 25                                                         | M12       | Stahl     | 2.6             |

## Harte Stufenaufsatzbacken

|                                                                                    | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|   | SHB-J 80    | 0133109    | 14        | 35        | 51        | 87        | 12        | 15.5      | 25        | 25        | M12       | Stahl     | 1.85           |
|  | SHB-J 82    | 0133110    | 14        | 32        | 38        | 79        | 12        | 16        | 25        | 25        | M12       | Stahl     | 1.2            |

## Segmentbacken

|                                                                                     | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | B1<br>[mm] | Ø D<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|------------|-------------|-----------|------------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | KMWB-SM 210 | 0132701    | 14        | 140       | 70         | 200         | 60        | 50         | 70        | 30        | 25        | M12       | Stahl     | 8.8            |
|                                                                                     | KMWB-SM 211 | 0132705    | 14        | 140       | 70         | 200         | 80        | 70         | 70        | 30        | 25        | M12       | Stahl     | 11.7           |
|  | KMWB-SA 210 | 0132801    | 14        | 140       | 50         | 200         | 58        | 48         | 72.5      | 35        | 25        | M12       | Aluminium | 3.3            |
|                                                                                     | KMWB-SA 211 | 0132805    | 14        | 140       | 50         | 200         | 80        | 70         | 72.5      | 35        | 25        | M12       | Aluminium | 4.5            |






Technische Beratung und Verkauf: Tel. +49-7133-103-2750

# SCHUNK Spannbacken für QJR08

## Verzahnte Stangen

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Werkstoff | m/Stück<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------------|
|  | JBM-ST 140  | 0114520    | 14        | 40        | 80        | 420       | Stahl     | 10.2            |
|                                                                                   | JBM-ST 141  | 0114521    | 14        | 60        | 60        | 420       | Stahl     | 11.2            |
|  | JBM-STA 140 | 0114522    | 14        | 40        | 80        | 420       | Aluminium | 3.7             |

## Weiche Aufsatzbacken

|                                                                                     | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a1<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|------------|-----------|-----------|-----------|-----------|----------------|
|    | KM-WBL 80   | 0132601    | 14        | 35        | 40        | 102       | 4          | 20        | 25        | M12       | Stahl     | 2.7            |
|                                                                                     | KM-WBL 81   | 0132607    | 14        | 40        | 80        | 102       | 4          | 20        | 25        | M12       | Stahl     | 6              |
|                                                                                     | KM-WBL 82   | 0132615    | 14        | 40        | 100       | 102       | 4          | 20        | 25        | M12       | Stahl     | 7.6            |
|   | KM-WB 84    | 0132126    | 14        | 35        | 60        | 95        |            | 24        | 25        | M12       | Stahl     | 3.9            |
|                                                                                     | KM-WB 85    | 0132127    | 14        | 40        | 80        | 95        |            | 24        | 25        | M12       | Stahl     | 6.1            |
|                                                                                     | KM-WB 88    | 0132139    | 14        | 35        | 40        | 95        |            | 24        | 25        | M12       | Stahl     | 2.7            |
|  | KM-WBAL 80  | 0132522    | 14        | 40        | 60        | 90        |            | 20        | 25        | M12       | Aluminium | 1.5            |



Technische Beratung und Verkauf: Tel. +49-7133-103-2750