




SCHUNK chuck jaws for HCLT 08


Jaw blanks

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Min. distance a (jaw tip up to first hole) [mm]	Min. distance b (first up to second hole) [mm]	Screws	Material	m/piece [kg]
	JBM 80	0114404	14	40	80	95	13	25	M12	Steel	2.4
	JBM 81	0114400	14	40	40	70	13	25	M12	Steel	0.9
	JBM 82	0114401	14	40	40	95	13	25	M12	Steel	1.2
	JBM 83	0114402	14	40	60	70	13	25	M12	Steel	1.3
	JBM 84	0114403	14	40	60	95	13	25	M12	Steel	1.7
	JBM 85	0114405	14	40	100	95	13	25	M12	Steel	2.9
	JBM 86	0114406	14	60	60	70	13	25	M12	Steel	2
	JBM 87	0114407	14	80	60	70	13	25	M12	Steel	2.6

Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	JBM-ST 140	0114520	14	40	80	420	Steel	10.2
	JBM-ST 141	0114521	14	60	60	420	Steel	11.2
	JBM-STA 140	0114522	14	40	80	420	Aluminum	3.7

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 80	0146101	14	24.5	8.5	25	M12	M12 x 35	70



Technical advice and sales: Tel. +49-7133-103-2750