




Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SRK-SM 114	0136151	8	8	70	8	47	53	17	M8	Stahl	2.5

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SRK 110	0136100	8	8	25	30	51	3	15	M6	Stahl	0.67
	SRK 114	0136115	8	8	22	47	55.3	1	17	M8	Stahl	0.9
	SRK-AL 114	0136141	8	8	22	47	55.3	1	17	M8	Aluminium	0.3

