



SCHUNK chuck jaws for AN-D 125



Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB 130	0121100	12	30	38	57	10	16	15	15	M8	Steel	0.7

Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 120	0112160	12	35	60	420	Steel	6.7
	SBM-ST 121	0112163	12	40	80	420	Steel	10.2
	SBM-STA 120	0112161	12	35	60	420	Aluminum	2.4

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB 130	0120100	12	30	38	55.5	10	16	M8	Steel	1.2
	SWB-AL 130	0168104	12	30	40	55	10	16	M8	Aluminum	0.45



Technical advice and sales: Tel. +49-7133-103-2750