



SCHUNK chuck jaws for AL-D 165



Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	13 - 40	182	SZA-ST 17-1	0175113	14	30	40	30	20	M10	Steel	1


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	30 - 60	182	SZA 17-1	0122260	14	30	47	20	M6	20	M10	Steel	1.2
	48 - 83	184	SZA 17-2	0122261	14	30	47	20	M6	20	M10	Steel	1
	74 - 110	185	SZA 17-3	0122262	14	30	47	20	M6	20	M10	Steel	1
	100 - 136	193	SZA 17-4	0122263	14	35	47	20	M6	20	M10	Steel	1.2



Full Grip Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB-SM 165	0169099	14	120	40	160	60	50	59.5	25	20	M10	Steel	5.6
	SWB-SA 165	0170099	14	120	40	165	58	48	59.5	25	20	M10	Aluminum	1.9

Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB 165	0121101	14	30	46	79.7	11	16.6	22	22	M10	Steel	1.3

Serrated bars




	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 140	0112165	14	35	60	420	Steel	6.6
	SBM-STA 140	0112166	14	35	60	420	Aluminum	2.4





Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for AL-D 165

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWBL 165	0120152	14	35	40	80	4	15	20	M10	Steel	2.1
	SWB 165	0120101	14	35	60	68		15	20	M10	Steel	2.5
	SWB-AL 165	0168105	14	35	60	80		15	20	M10	Aluminum	1.2

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NKS 1	0143104	14	18.5	6.5		M10	M10 x 25	50
	NKA 1	0145103	14	18.5	6.5	20	M10	M10 x 25	50



Technical advice and sales: Tel. +49-7133-103-2750