

SCHUNK Spannbacken für HG-F 315

Grundbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	m/Satz [kg]
	SFG 315	0157103	26	12	32		43	125		54	M12x1.5	3.1
	SFGL 315	0157123	26	12	32		43	160		54	M12x1.5	4
	SFG-V 315	0157153	26	12	32		46	125		54	M12x1.5	3.1
	STB 315-2	0156103	21		32	54	75	125			M16	9.3
	STN 315-4	0160503	21		32	45	55	110	13	28	M16	4.5

Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHF 315	0155103	12	26	36	62	56	105	15	54	M12	Stahl	3.3

Harte Stufenblockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Werkstoff	m/Satz [kg]
	STF 315	0161103	32	81	46	129	15	Stahl	5.5

Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	191 - 302	390	I	SZKA 324	0139169	12	26	40	53	25	M8	54	M12	Stahl	2.8
	44 - 102	370	II	SZKA 321	0139166	12	26	40	53	25	M8	54	M12	Stahl	3.1
	119 - 210	370	II	SZKA 324	0139169	12	26	40	53	25	M8	54	M12	Stahl	2.8


Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	93 - 190	383	I	SZKI 319	0166162	12	26	40	53	25	M8	54	M12	Stahl	3.9
	189 - 299	383	I	SZKI 322	0166165	12	26	40	53	25	M8	54	M12	Stahl	2.7
	118 - 207	369	II	SZKI 322	0166165	12	26	40	53	25	M8	54	M12	Stahl	2.7




Technische Beratung und Verkauf: Tel. +49-7133-103-2750



Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	16 - 86	370	II	SZKA-ST 311	0182156	12	26	32	50	40	54	M12	Stahl	2.2



Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	108 - 195	375	PNK-S 400-1	0190568	99	50	3.7
	182 - 267	460	PNK-S 400-3	0190570	99	50	5.5
	228 - 297	459	PNK-S 400-5	0190572	99	50	5.4

Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA-SM 315	0173103	12	26	240	120	320	75	69	60	110	54	54	M12	Stahl	28.9
	SFA-SA 315	0174103	12	26	240	80	320	75	69	60	117	64	54	M12	Aluminium	10.8

Weiche Aufsatzbacken


	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA 315	0153103	12	26	35	60	54		145	45	54	M12	Stahl	5.6
	SFA 315-C1	0154108	12	26	40		60	54	110	30	54	M12	Stahl	4.9
	SFA 315-C2	0154109	12	26	40		60	54	145	30	54	M12	Stahl	6.6
	SFA 315-C3	0154110	12	26	40		100	94	145	30	54	M12	Stahl	11.4
	SFA 315-C4	0154111	12	26	40		120	114	145	30	54	M12	Stahl	13.8
	SFA 315-C5	0154112	12	26	40		150	144	145	30	54	M12	Stahl	17.5
	SFA 315-C51	0154123	12	26	50		80	74	145	30	54	M12	Stahl	11.4
	SFA 315-C6	0154113	12	26	60		60	54	110	30	54	M12	Stahl	7.6
	SFA 315-C7	0154114	12	26	80		60	54	110	30	54	M12	Stahl	10.3
	SFA 315-C8	0154115	12	26	80		80	74	110	30	54	M12	Stahl	14.2
	SFA-AL 315	0172104	12	26	40	60	54		145	45	54	M12	Aluminium	2.4



Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für HG-F 315

Weiche Blockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	Werkstoff	m/Satz [kg]
	SMB 315	0163103	32	81	46	140	Stahl	7.5
	SMB-H 315	0163203	32	135	100	140	Stahl	13



Technische Beratung und Verkauf: Tel. +49-7133-103-2750