



SCHUNK Spannbacken für KNCS 140


Grundbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Schrauben	m/Satz [kg]
	GBK 140	0159099	18	8	20	27.5	56	32	M8	0.4
	GBK-V 140	0159157	18	8	20	27.5	56	32	M8	0.4


Harte Stufenblockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Werkstoff	m/Satz [kg]
	GST 140-160 I	0162097	20	43.5	22	58	7	Stahl	0.7
	GST 140-160 II	0162098	20	43.5	22	58	7	Stahl	0.7

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA 140	0153098	8	18	20	40	36		69	25	32	M8	Stahl	0.9
	SFA 140-C1	0154129	8	18	30		45	41	63	19	32	M8	Stahl	1.7

Weiche Blockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	Werkstoff	m/Satz [kg]
	UVB 160	0164106	20	55.5	35	65	Stahl	1.6



Technische Beratung und Verkauf: Tel. +49-7133-103-2750