





SCHUNK chuck jaws for KNCS 200


Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	m/set [kg]
	GBK 200	0159100	20	10	22		29.5	85		40	M8	1
	GBKL 200	0159120	20	10	22		29.5	105		40	M8	1.2
	GBK-V 200	0159150	20	10	22		29.5	85		40	M8	1
	STB-G 200-1	0160655	17		22	45	59	85			M12	3
	STNJ 200-5	0160650	14		22	40	47	95	10	25	M12	2.6


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	17 - 59	237	II	SZKA-ST 201	0182152	10	20	22	45	37	40	M8	Steel	0.9

Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	53 - 84	236	I	SZKI 209	0166154	10	20	30	45	20	M6	40	M8	Steel	1.7
	110 - 154	236	I	SZKI 211	0166156	10	20	30	45	20	M6	40	M8	Steel	1.4
	82 - 116	236	II	SZKI 211	0166156	10	20	30	45	20	M6	40	M8	Steel	1.4

Claw jaws for O.D. clamping



	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	27 - 70	237	I	SZKA 212	0139153	10	20	26	45	25	M6	40	M8	Steel	1.4
	102 - 145	237	I	SZKA 213	0139154	10	20	30	45	25	M6	40	M8	Steel	1.3
	137 - 180	242	I	SZKA 216	0139159	10	20	30	45	25	M6	40	M8	Steel	1.2
	66 - 108	237	II	SZKA 213	0139154	10	20	30	45	25	M6	40	M8	Steel	1.3




Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KNCS 200


Full Grip Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA-SM 200	0173101	10	20	140	64	200	60	56	50	70	27	40	M8	Steel	9
	SFA-SM 201	0173105	10	20	140	64	200	80	76	70	70	27	40	M8	Steel	12.5
	SFA-SA 200	0174101	10	20	140	50	200	58	54	48	72.5	32	40	M8	Aluminum	3.5
	SFA-SA 201	0174105	10	20	140	50	200	80	76	70	72.5	32	40	M8	Aluminum	4.7


Hard Stepped Block Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Material	m/set [kg]
	GST 201	0162106	22	54	29	84.9	8	Steel	1.6

Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 200	0155101	10	20	22	42	38	71.7	10	40	M8	Steel	2.4

Pendulum jaws





	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	53 - 87	224	PNK-G 200-2	0190659	76	36	1.2
	78 - 112	233	PNK-G 200-6	0190663	76	36	1.6
	108 - 142	233	PNK-G 200-8	0190665	76	36	1.8






Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KNCS 200

QUENTES fiberglass jaws

	Clamping range ØD	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Max. tightening torque [Nm]	Screws	m/set [kg]
	55 - 129	TRQK 200-2	0150010	10	20	40	58	72	40		M8	0.76
	20 - 51	TRQK 200-1	0150009	10	20	38	54	91	40		M8	0.74
		QUENTES 10-3	0150100							8		
		QUENTES 20-3	0150200							8		

Soft Monoblock Jaws



	Description	ID	B [mm]	B1 [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	Material	m/set [kg]
	UVB 200	0164100	22		65	40		84	Steel	2.7
	UVB-H 200	0164116	22		85	60		84	Steel	3.2
	UVB-B 200	0164113	22	40	65	38		84	Steel	3.9
	UVB-HS 200	0164119	22		85	60	29	84	Steel	2.67



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KNCS 200

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 200	0153101	10	20	22	47	43		105	35	40	M8	Steel	2
	SFA 200-C1	0154100	10	20	30		55.5	51.5	100	23	40	M8	Steel	3.2
	SFA 200-C2	0154124	10	20	22		55.5	51.5	100	23	40	M8	Steel	2.2
	SFA 200-C3	0154128	10	20	40		40	36	70	23	40	M8	Steel	2.1
	SFA 200-C4	0154130	10	20	40		60	56	85	23	40	M8	Steel	4
	SFA 200-C5	0154132	10	20	40		80	76	95	23	40	M8	Steel	6.1
	SFA-AL 200	0172102	10	20	25	50	46		105	35	40	M8	Aluminum	0.9



Technical advice and sales: Tel. +49-7133-103-2750