




SCHUNK chuck jaws for KNCS-N 260


Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	m/set [kg]
	GBK 250	0159101	20	12	26		37	104		40	M12	1.8
	GBKL 250	0159121	20	12	26		37	125		40	M12	2.4
	GBK-V 250	0159151	20	12	26		37	104		40	M12	1.8
	STB-G 250-2	0160657	21		26	50	71	104			M16	5.2
	STN 250-5	0160651	16		26	40	49	110	10	30	M12	2.9
	STN 250-5	0160600	17		26	40	48	86	10	22	M12	2.6
	STN 250-6	0160601	21		26	45	52	110	13	28	M16	4


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	14 - 76	305	II	SZKA-ST 251	0182154	12	20	26	45	35	40	M12	Steel	1.2

Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	69 - 132	303	I	SZKI 261	0166158	12	20	40	50	25	M6	40	M12	Steel	2.8
	176 - 251	305	I	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Steel	2.2
	114 - 187	304	II	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Steel	2.2

Claw jaws for O.D. clamping



	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	139 - 213	308	I	SZKA 266	0139163	12	20	40	50	25	M6	40	M12	Steel	1.9
	173 - 247	321	I	SZKA 268	0139165	12	20	40	50	25	M6	40	M12	Steel	2.2
	31 - 93	305	II	SZKA 263	0139160	12	20	30	50	25	M6	40	M12	Steel	1.4
	86 - 150	305	II	SZKA 266	0139163	12	20	40	50	25	M6	40	M12	Steel	1.9




Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KNCS-N 260


Full Grip Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA-SM 250	0173102	12	20	180	70	250	60	55	45	90	44	40	M12	Steel	12.8
	SFA-SM 251	0173106	12	20	180	70	250	80	75	65	90	44	40	M12	Steel	16.8
	SFA-SA 250	0174102	12	20	180	70	250	58	53	43	87.5	44	40	M12	Aluminum	4.8
	SFA-SA 251	0174106	12	20	180	70	250	80	75	65	87.5	44	40	M12	Aluminum	6.4


Hard Stepped Block Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Material	m/set [kg]
	GST 251	0162105	26	65	36	107.5	10	Steel	2.8

Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 250	0155102	12	20	30	55	50	90	14	40	M12	Steel	1.9

Pendulum jaws





	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	57 - 91	274	PNK-G 250-2	0190601	86	40	1.8
	85 - 109	290	PNK-G 250-6	0190605	86	40	2.2
	119 - 176	300	PNK-G 250-8	0190607	86	40	2.4
	128 - 185	300	PNK-G 250-10	0190609	86	40	2.5






Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KNCS-N 260

QUENTES fiberglass jaws

	Clamping range ØD	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Max. tightening torque [Nm]	Screws	m/set [kg]
	55 - 180	TRQK 250-2	0150012	12	20	40	57	72	40		M12	0.7
	20 - 95	TRQK 250-1	0150011	12	20	38	53	98	40		M12	0.8
		QUENTES 10-3	0150100							8		
		QUENTES 20-3	0150200							8		

Soft Monoblock Jaws



	Description	ID	B [mm]	B1 [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	Material	m/set [kg]
	UVB 250	0164101	26		84	55		99	Steel	4.8
	UVB-H 250	0164117	26		115	86		99	Steel	6.6
	UVB-B 250	0164114	26	46	84	52		99	Steel	7.2
	UVB-HS 250	0164120	26		115	86	48	99	Steel	5.25



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KNCS-N 260

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 250	0153102	12	20	30	55.5	50.5		125	35	40	M12	Steel	3.7
	SFA 250-C1	0154101	12	20	40		60	55	90	26	40	M12	Steel	3.9
	SFA 250-C2	0154102	12	20	40		60	55	125	26	40	M12	Steel	5.6
	SFA 250-C3	0154103	12	20	40		80	75	125	26	40	M12	Steel	7.7
	SFA 250-C4	0154104	12	20	40		100	95	125	26	40	M12	Steel	9.8
	SFA 250-C5	0154105	12	20	40		120	115	125	26	40	M12	Steel	11.8
	SFA 250-C6	0154106	12	20	60		60	55	90	26	40	M12	Steel	6
	SFA 250-C7	0154107	12	20	80		60	55	90	26	40	M12	Steel	8.5
	SFA 250-C8	0154134	12	20	80		100	95	125	26	40	M12	Steel	20.9
	SFA-AL 250	0172103	12	20	40	60	55		125	35	40	M12	Aluminum	2.1



Technical advice and sales: Tel. +49-7133-103-2750