



SCHUNK chuck jaws for KNCS-N 170


Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	GBK 160	0159106	18	8	20	27.5	65	32	M8	0.6
	GBK-V 160	0159156	18	8	20	27.5	65	32	M8	0.6


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	12 - 44	193	II	SZKA-ST 161	0182150	8	18	22	40	30	32	M8	Steel	0.8



Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	47 - 72	193	I	SZKI 167	0166150	8	18	35	40	20	M6	32	M8	Steel	0.9
	52 - 77	193	I	SZKI 168	0166151	8	18	35	40	20	M6	32	M8	Steel	1.4
	99 - 132	193	I	SZKI 169	0166152	8	18	30	40	20	M6	32	M8	Steel	1.3
	82 - 114	193	II	SZKI 169	0166152	8	18	30	40	20	M6	32	M8	Steel	1.3

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	87 - 120	200	I	SZKA 163	0165146	8	18	40	40	20	M6	32	M8	Steel	1
	39 - 72	193	I	SZKA 169	0165174	8	18	26	40	20	M6	32	M8	Steel	1
	69 - 102	193	II	SZKA 163	0165146	8	18	40	40	20	M6	32	M8	Steel	1
	120 - 153	214	II	SZKA 167	0165150	8	18	30	40	20	M6	32	M8	Steel	1.3

Full Grip Jaws


	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA-SM 160	0173100	8	18	120	40	160	50	46	40	60	23	32	M8	Steel	4.8
	SFA-SA 160	0174100	8	18	120	40	165	50	46	40	59.5	23	32	M8	Aluminum	1.8




Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KNCS-N 170



Hard Stepped Block Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Material	m/set [kg]
	GST 175	0162099	20	46	24	66.6	7	Steel	0.9


Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 160	0155100	8	18	20	36.5	32.5	63	7.5	32	M8	Steel	0.6



QUENTES fiberglass jaws

	Clamping range ØD	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Max. tightening torque [Nm]	Screws	m/set [kg]
	20 - 73	TRQK 160	0150024	8	18	38	54	56	32		M8	0.5
		QUINTES 10-3	0150100							8		

Soft Monoblock Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	Material	m/set [kg]
	UVB 160	0164106	20	55.5	35	65	Steel	1.6

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 160	0153100	8	18	20	40	36		85	25	32	M8	Steel	1.2
	SFA 160-C1	0154121	8	18	30		55.5	51.5	85	19	32	M8	Steel	2.7
	SFA 160-C2	0154127	8	18	35		40	36	63	19	32	M8	Steel	1.6
	SFA 160-C3	0154131	8	18	40		60	56	70	19	32	M8	Steel	3.3
	SFA 160-C4	0154133	8	18	40		80	76	85	19	32	M8	Steel	5.6
	SFA-AL 160	0172100	8	18	25	50	46		85	25	32	M8	Aluminum	0.7



Technical advice and sales: Tel. +49-7133-103-2750