



SCHUNK chuck jaws for KNCS–NB 800

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 400	0153104	18	30	50	80	73		180	50	60	M16	Steel	13.5
	SFA 400–C1	0154116	18	30	60		80	73	130	35	60	M16	Steel	11.8
	SFA 400–C3	0154118	18	30	60		100	93	155	35	60	M16	Steel	21.5
	SFA 400–C4	0154119	18	30	60		120	113	155	35	60	M16	Steel	22.4
	SFA 400–C5	0154120	18	30	80		80	73	130	35	60	M16	Steel	16
	SFA 400–C6	0154125	18	30	58		180	173	160	35	60	M16	Steel	35.1
	SFA 400–C7	0154135	18	30	96		115	108	115	35	60	M16	Steel	25.9
	SFA-AL 400	0172105	18	30	50	80	73		180	50	60	M16	Aluminum	5.1



Technical advice and sales: Tel. +49-7133-103-2750