



SCHUNK chuck jaws for KNCS-NB 630


Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	EWB-MT 630	0160795	40	24	75	61	203	82	M20	18.5



Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	350 - 540	640	I	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5
	103 - 251	640	II	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Steel	6
	157 - 341	640	II	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	331 - 521	641	I	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1
	50 - 220	641	II	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Steel	6
	133 - 322	641	II	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1

Full Grip Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA-SM 400	0173104	18	30	330	150	440	85	78	55	160	95	60	M16	Steel	55.6
	SFA-SA 400	0174104	18	30	330	150	440	90	83	60	160	95	60	M16	Aluminum	22.8

Hard Stepped Top Jaws



	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 400	0155104	18	30	45	82	75	130	20	60	M16	Steel	6.8
	SHF 630	0155106	24	40	65	105	97	185	30	82	M20	Steel	18



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KNCS–NB 630

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 400	0153104	18	30	50	80	73		180	50	60	M16	Steel	13.5
	SFA 630	0153106	24	40	65	118	110		260	70	82	M20	Steel	39.6
	SFA 400–C1	0154116	18	30	60		80	73	130	35	60	M16	Steel	11.8
	SFA 400–C3	0154118	18	30	60		100	93	155	35	60	M16	Steel	21.5
	SFA 400–C4	0154119	18	30	60		120	113	155	35	60	M16	Steel	22.4
	SFA 400–C5	0154120	18	30	80		80	73	130	35	60	M16	Steel	16
	SFA 400–C6	0154125	18	30	58		180	173	160	35	60	M16	Steel	35.1
	SFA 400–C7	0154135	18	30	96		115	108	115	35	60	M16	Steel	25.9
	SFA-AL 400	0172105	18	30	50	80	73		180	50	60	M16	Aluminum	5.1
	SFA-AL 630	0172106	24	40	65	118	110		260	70	82	M20	Aluminum	14.8



Technical advice and sales: Tel. +49-7133-103-2750