



SCHUNK chuck jaws for KNCS–NB 500


Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	EWB-MT 500	0160794	30	18	62	57	160	60	M16	10.7



Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	281 – 449	551	I	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5
	103 – 238	549	II	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Steel	6
	161 – 328	549	II	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	262 – 430	552	I	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1
	50 – 207	550	II	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Steel	6
	142 – 309	550	II	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1

Full Grip Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA-SM 400	0173104	18	30	330	150	440	85	78	55	160	95	60	M16	Steel	55.6
	SFA-SA 400	0174104	18	30	330	150	440	90	83	60	160	95	60	M16	Aluminum	22.8

Hard Stepped Top Jaws



	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 400	0155104	18	30	45	82	75	130	20	60	M16	Steel	6.8



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KNCS–NB 500

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 400	0153104	18	30	50	80	73		180	50	60	M16	Steel	13.5
	SFA 400–C1	0154116	18	30	60		80	73	130	35	60	M16	Steel	11.8
	SFA 400–C3	0154118	18	30	60		100	93	155	35	60	M16	Steel	21.5
	SFA 400–C4	0154119	18	30	60		120	113	155	35	60	M16	Steel	22.4
	SFA 400–C5	0154120	18	30	80		80	73	130	35	60	M16	Steel	16
	SFA 400–C6	0154125	18	30	58		180	173	160	35	60	M16	Steel	35.1
	SFA 400–C7	0154135	18	30	96		115	108	115	35	60	M16	Steel	25.9
	SFA-AL 400	0172105	18	30	50	80	73		180	50	60	M16	Aluminum	5.1



Technical advice and sales: Tel. +49-7133-103-2750