



SCHUNK chuck jaws for KNCS-NB 400


Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	EWB-MT 400	0160793	30	18	50	51	125	60	M16	6.1


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	36 - 167	450	II	SZKA-ST 311	0182156	12	26	32	50	40	54	M12	Steel	2.2



Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	126 - 256	449	I	SZKI 319	0166162	12	26	40	53	25	M8	54	M12	Steel	3.9
	234 - 365	449	I	SZKI 322	0166165	12	26	40	53	25	M8	54	M12	Steel	2.7
	221 - 351	455	I	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5
	156 - 287	449	II	SZKI 322	0166165	12	26	40	53	25	M8	54	M12	Steel	2.7
	107 - 214	455	II	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Steel	6
	174 - 304	455	II	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	237 - 368	457	I	SZKA 324	0139169	12	26	40	53	25	M8	54	M12	Steel	2.8
	201 - 332	455	I	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1
	53 - 182	450	II	SZKA 321	0139166	12	26	40	53	25	M8	54	M12	Steel	3.1
	159 - 290	450	II	SZKA 324	0139169	12	26	40	53	25	M8	54	M12	Steel	2.8
	57 - 183	455	II	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Steel	6
	154 - 285	455	II	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1

Full Grip Jaws


	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA-SM 315	0173103	12	26	240	120	320	75	69	60	110	54	54	M12	Steel	28.9
	SFA-SM 400	0173104	18	30	330	150	440	85	78	55	160	95	60	M16	Steel	55.6
	SFA-SA 315	0174103	12	26	240	80	320	75	69	60	117	64	54	M12	Aluminum	10.8
	SFA-SA 400	0174104	18	30	330	150	440	90	83	60	160	95	60	M16	Aluminum	22.8




Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KNCS-NB 400



Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 315	0155103	12	26	36	62	56	105	15	54	M12	Steel	3.3
	SHF 400	0155104	18	30	45	82	75	130	20	60	M16	Steel	6.8

Soft Monoblock Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	Material	m/set [kg]
	EWM 400	0164133	50	100	66	142	Steel	16

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 315	0153103	12	26	35	60	54		145	45	54	M12	Steel	5.6
	SFA 400	0153104	18	30	50	80	73		180	50	60	M16	Steel	13.5
	SFA 315-C1	0154108	12	26	40		60	54	110	30	54	M12	Steel	4.9
	SFA 315-C2	0154109	12	26	40		60	54	145	30	54	M12	Steel	6.6
	SFA 315-C3	0154110	12	26	40		100	94	145	30	54	M12	Steel	11.4
	SFA 315-C4	0154111	12	26	40		120	114	145	30	54	M12	Steel	13.8
	SFA 315-C5	0154112	12	26	40		150	144	145	30	54	M12	Steel	17.5
	SFA 315-C51	0154123	12	26	50		80	74	145	30	54	M12	Steel	11.4
	SFA 315-C6	0154113	12	26	60		60	54	110	30	54	M12	Steel	7.6
	SFA 315-C7	0154114	12	26	80		60	54	110	30	54	M12	Steel	10.3
	SFA 315-C8	0154115	12	26	80		80	74	110	30	54	M12	Steel	14.2
	SFA 400-C1	0154116	18	30	60		80	73	130	35	60	M16	Steel	11.8
	SFA 400-C3	0154118	18	30	60		100	93	155	35	60	M16	Steel	21.5
	SFA 400-C4	0154119	18	30	60		120	113	155	35	60	M16	Steel	22.4
	SFA 400-C5	0154120	18	30	80		80	73	130	35	60	M16	Steel	16
	SFA 400-C6	0154125	18	30	58		180	173	160	35	60	M16	Steel	35.1
	SFA-AL 315	0172104	12	26	40	60	54		145	45	54	M12	Aluminum	2.4
	SFA-AL 400	0172105	18	30	50	80	73		180	50	60	M16	Aluminum	5.1



Technical advice and sales: Tel. +49-7133-103-2750