



SCHUNK chuck jaws for KNCS–NBX 1000

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 400	0153104	18	30	50	80	73		180	50	60	M16	Steel	13.5
	SFA 400-C1	0154116	18	30	60		80	73	130	35	60	M16	Steel	11.8
	SFA 400-C3	0154118	18	30	60		100	93	155	35	60	M16	Steel	21.5
	SFA 400-C4	0154119	18	30	60		120	113	155	35	60	M16	Steel	22.4
	SFA 400-C5	0154120	18	30	80		80	73	130	35	60	M16	Steel	16
	SFA 400-C6	0154125	18	30	58		180	173	160	35	60	M16	Steel	35.1
	SFA 400-C7	0154135	18	30	96		115	108	115	35	60	M16	Steel	25.9
	SFA-AL 400	0172105	18	30	50	80	73		180	50	60	M16	Aluminum	5.1



Technical advice and sales: Tel. +49-7133-103-2750