




# SCHUNK chuck jaws for ODL 220


## Full Grip Jaws

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | B1<br>[mm] | Ø D<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/set |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-------------|-----------|------------|-----------|-----------|-----------|--------|----------|-------|
|  | SWB-SM 200  | 0169101 | 17        | 140       | 64         | 200         | 60        | 50         | 69.5      | 35        | 22        | M12    | Steel    | 8.6   |
|                                                                                   | SWB-SM 201  | 0169106 | 17        | 140       | 64         | 200         | 75        | 65         | 69.5      | 35        | 22        | M12    | Steel    | 10.8  |
|  | SWB-SA 200  | 0170101 | 17        | 140       | 50         | 200         | 58        | 48         | 72.5      | 35        | 22        | M12    | Aluminum | 3.4   |
|                                                                                   | SWB-SA 201  | 0170106 | 17        | 140       | 50         | 200         | 75        | 65         | 72.5      | 35        | 22        | M12    | Aluminum | 4.2   |

## Hard Stepped Top Jaws

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|---------------|
|  | SHB 210     | 0121102 | 17        | 40        | 49        | 84.3      | 12        | 28.7      | 19        | 19        | M12    | Steel    | 2             |

## Jaw blanks





|                                                                                     | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Min. distance<br>a (jaw tip up<br>to first hole)<br>[mm] | Min. distance<br>b (first up to<br>second hole)<br>[mm] | Screws | Material | m/piece<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|----------------------------------------------------------|---------------------------------------------------------|--------|----------|-----------------|
|  | SBM 31      | 0112100 | 17        | 40        | 40        | 70        | 12                                                       | 22                                                      | M12    | Steel    | 0.9             |
|                                                                                     | SBM 32      | 0112101 | 17        | 40        | 40        | 90        | 12                                                       | 22                                                      | M12    | Steel    | 1.1             |
|                                                                                     | SBM 33      | 0112102 | 17        | 40        | 40        | 105       | 12                                                       | 22                                                      | M12    | Steel    | 1.2             |
|                                                                                     | SBM 34      | 0112103 | 17        | 40        | 60        | 70        | 12                                                       | 22                                                      | M12    | Steel    | 1.3             |
|                                                                                     | SBM 35      | 0112104 | 17        | 40        | 60        | 90        | 12                                                       | 22                                                      | M12    | Steel    | 1.7             |
|                                                                                     | SBM 36      | 0112105 | 17        | 40        | 60        | 105       | 12                                                       | 22                                                      | M12    | Steel    | 2               |
|                                                                                     | SBM 361     | 0112136 | 17        | 40        | 60        | 120       | 12                                                       | 22                                                      | M12    | Steel    | 2.2             |
|                                                                                     | SBM 3610    | 0112107 | 17        | 40        | 100       | 90        | 12                                                       | 22                                                      | M12    | Steel    | 2.7             |
|                                                                                     | SBM 3612    | 0112108 | 17        | 40        | 120       | 90        | 12                                                       | 22                                                      | M12    | Steel    | 3.4             |
|                                                                                     | SBM 3615    | 0112139 | 17        | 50        | 80        | 90        | 12                                                       | 22                                                      | M12    | Steel    | 2.7             |
|                                                                                     | SBM 368     | 0112106 | 17        | 40        | 80        | 90        | 12                                                       | 22                                                      | M12    | Steel    | 2.3             |
|                                                                                     | SBM 37      | 0112109 | 17        | 60        | 60        | 70        | 12                                                       | 22                                                      | M12    | Steel    | 1.9             |
|                                                                                     | SBM 38      | 0112110 | 17        | 60        | 60        | 90        | 12                                                       | 22                                                      | M12    | Steel    | 2.4             |
|                                                                                     | SBM 40      | 0112111 | 17        | 80        | 60        | 90        | 12                                                       | 22                                                      | M12    | Steel    | 3.3             |





Technical advice and sales: Tel. +49-7133-103-2750

# SCHUNK chuck jaws for ODL 220

## QUENTES fiberglass jaws

|                                                                                   | Clamping range ØD | Description  | ID      | N [mm] | B [mm] | H [mm] | L [mm] | b [mm] | Max. tightening torque [Nm] | Screws | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------------|--------------|---------|--------|--------|--------|--------|--------|-----------------------------|--------|------------|
|  | 20 - 65           | TRQ 200-1    | 0150001 | 17     | 40     | 55     | 70     | 19     |                             | M12    | 0.66       |
|  | 85 - 169          | TRQ 200-2    | 0150002 | 17     | 40     | 64     | 79     | 19     |                             | M12    | 0.93       |
|  |                   | QUENTES 10-3 | 0150100 |        |        |        |        |        | 8                           |        |            |
|  |                   | QUENTES 20-3 | 0150200 |        |        |        |        |        | 8                           |        |            |

## Serrated bars

|                                                                                     | Description | ID      | N [mm] | B [mm] | H [mm] | L [mm] | Material | m/piece [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|----------|--------------|
|  | SBM-ST 170  | 0112170 | 17     | 40     | 60     | 420    | Steel    | 7.6          |
|                                                                                     | SBM-ST 171  | 0112171 | 17     | 40     | 80     | 420    | Steel    | 10.2         |
|                                                                                     | SBM-ST 172  | 0112172 | 17     | 40     | 100    | 420    | Steel    | 12.8         |
|  | SBM-STA 170 | 0112173 | 17     | 40     | 60     | 420    | Aluminum | 2.8          |



Technical advice and sales: Tel. +49-7133-103-2750

# SCHUNK chuck jaws for ODL 220

## Soft Top Jaws

|  | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a1<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|--|-------------|---------|-----------|-----------|-----------|-----------|------------|-----------|-----------|--------|----------|---------------|
|  | SWBL 200    | 0120153 | 17        | 35        | 40        | 98        | 4          | 15        | 22        | M12    | Steel    | 2.6           |
|  | CWB 200     | 0100006 | 17        | 40        | 40        | 90        |            | 25        | 22        | M12    | Steel    | 2.7           |
|  | SWB 200     | 0120104 | 17        | 40        | 60        | 90        |            | 25        | 22        | M12    | Steel    | 4.1           |
|  | SWB-AL 200  | 0168101 | 17        | 40        | 60        | 90        |            | 25        | 22        | M12    | Aluminum | 1.5           |

## T-nut

|  | Description | ID      | S<br>[mm] | H<br>[mm] | H1<br>[mm] | G   | Cyl.-screw | Max. adm.<br>tightening torque<br>[Nm] |
|--|-------------|---------|-----------|-----------|------------|-----|------------|----------------------------------------|
|  | NS 121      | 0140113 | 17        | 22.3      | 8.3        | M12 | M12 x 30   | 70                                     |



Technical advice and sales: Tel. +49-7133-103-2750