




SCHUNK Spannbacken für RMG 315


Grundbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	m/Satz [kg]
	GBK 400	0159103	26	12	32		43	125		54	M12	3
	GBK-V 400	0159158	26	12	32		43	125		54	M12	3
	STB-G 315-2	0160659	21		32	54	76	115			M16	7.5
	STNJ 315-5	0160652	18		32	50	54	120	15	30	M14	4.9
	STNJ 315-6	0160665	21		32	50	58	125	17.5	30	M16	5.5
	STN 315-6	0160603	21		32	45	56	110	13	28	M16	4.5



Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHF 315	0155103	12	26	36	62	56	105	15	54	M12	Stahl	3.3

Harte Stufenblockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Werkstoff	m/Satz [kg]
	GST 400	0162103	32	70	36	136.4	11	Stahl	4.6

Segmentbacken



	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA-SM 315	0173103	12	26	240	120	320	75	69	60	110	54	54	M12	Stahl	28.9
	SFA-SA 315	0174103	12	26	240	80	320	75	69	60	117	64	54	M12	Aluminium	10.8




Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für RMG 315

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA 315	0153103	12	26	35	60	54		145	45	54	M12	Stahl	5.6
	SFA 315-C1	0154108	12	26	40		60	54	110	30	54	M12	Stahl	4.9
	SFA 315-C2	0154109	12	26	40		60	54	145	30	54	M12	Stahl	6.6
	SFA 315-C3	0154110	12	26	40		100	94	145	30	54	M12	Stahl	11.4
	SFA 315-C4	0154111	12	26	40		120	114	145	30	54	M12	Stahl	13.8
	SFA 315-C5	0154112	12	26	40		150	144	145	30	54	M12	Stahl	17.5
	SFA 315-C51	0154123	12	26	50		80	74	145	30	54	M12	Stahl	11.4
	SFA 315-C6	0154113	12	26	60		60	54	110	30	54	M12	Stahl	7.6
	SFA 315-C7	0154114	12	26	80		60	54	110	30	54	M12	Stahl	10.3
	SFA 315-C8	0154115	12	26	80		80	74	110	30	54	M12	Stahl	14.2
	SFA-AL 315	0172104	12	26	40	60	54		145	45	54	M12	Aluminium	2.4

Weiche Blockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	Werkstoff	m/Satz [kg]
	UVB 400	0164103	32	100	66	148	Stahl	10



Technische Beratung und Verkauf: Tel. +49-7133-103-2750