






SCHUNK chuck jaws for RMG 250


Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	m/set [kg]
	GBK 250	0159101	20	12	26		37	104		40	M12	1.8
	GBK 250	0159121	20	12	26		37	125		40	M12	2.4
	GBK-V 250	0159151	20	12	26		37	104		40	M12	1.8
	STB-G 250-2	0160657	21		26	50	71	104			M16	5.2
	STN 250-5	0160651	16		26	40	49	110	10	30	M12	2.9
	STN 250-5	0160600	17		26	40	48	86	10	22	M12	2.6
	STN 250-6	0160601	21		26	45	52	110	13	28	M16	4


Full Grip Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA-SM 250	0173102	12	20	180	70	250	60	55	45	90	44	40	M12	Steel	12.8
	SFA-SM 251	0173106	12	20	180	70	250	80	75	65	90	44	40	M12	Steel	16.8
	SFA-SA 250	0174102	12	20	180	70	250	58	53	43	87.5	44	40	M12	Aluminum	4.8
	SFA-SA 251	0174106	12	20	180	70	250	80	75	65	87.5	44	40	M12	Aluminum	6.4

Hard Stepped Block Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Material	m/set [kg]
	GST 251	0162105	26	65	36	107.5	10	Steel	2.8

Hard Stepped Top Jaws




	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 250	0155102	12	20	30	55	50	90	14	40	M12	Steel	1.9





Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for RMG 250

Soft Monoblock Jaws

	Description	ID	B [mm]	B1 [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	Material	m/set [kg]
	UVB 250	0164101	26		84	55		99	Steel	4.8
	UVB-H 250	0164117	26		115	86		99	Steel	6.6
	UVB-B 250	0164114	26	46	84	52		99	Steel	7.2
	UVB-HS 250	0164120	26		115	86	48	99	Steel	5.25

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 250	0153102	12	20	30	55.5	50.5		125	35	40	M12	Steel	3.7
	SFA 250-C1	0154101	12	20	40		60	55	90	26	40	M12	Steel	3.9
	SFA 250-C2	0154102	12	20	40		60	55	125	26	40	M12	Steel	5.6
	SFA 250-C3	0154103	12	20	40		80	75	125	26	40	M12	Steel	7.7
	SFA 250-C4	0154104	12	20	40		100	95	125	26	40	M12	Steel	9.8
	SFA 250-C5	0154105	12	20	40		120	115	125	26	40	M12	Steel	11.8
	SFA 250-C6	0154106	12	20	60		60	55	90	26	40	M12	Steel	6
	SFA 250-C7	0154107	12	20	80		60	55	90	26	40	M12	Steel	8.5
	SFA 250-C8	0154134	12	20	80		100	95	125	26	40	M12	Steel	20.9
	SFA-AL 250	0172103	12	20	40	60	55		125	35	40	M12	Aluminum	2.1



Technical advice and sales: Tel. +49-7133-103-2750