




SCHUNK Spannbacken für KFD-HS 130


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB-FR 130	0121109	10	26	37.5	58	10	11.6	12	12	M6	Stahl	0.4




Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	FR-SM 130	0120700	10	100	35	130	40	35	50	15	12	12	M6	Stahl	3
	FR-SA 130	0120650	10	100	35	130	48	43	47.4	15	12	12	M6	Aluminium	1.3

Verzahnte Stangen

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	SBM-ST 100	0112150	10	35	60	420	Stahl	6.7

Weiche Aufsatzbacken


	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWB-FR 130	0120400	10	25	30	55.5	3	11	12	12	M6	Stahl	0.8
	SWB-FR 133	0120410	10	32	32	62	2	9	12	12	M6	Stahl	1.2
	SWB-FR 132	0132141	10	22	47	53		9	12	12	M6	Stahl	1
	FR-AL 130	0120600	10	25	45	53	3	9	12	12	M6	Aluminium	0.4



Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für KFD-HS 130

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmo- ment [Nm]
	NK 60	0147104	10	13.7	5.5	12	M6	M6 x 18	16



Technische Beratung und Verkauf: Tel. +49-7133-103-2750