




# SCHUNK chuck jaws for KFD-HS 140


## Full Grip Jaws

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | B1<br>[mm] | Ø D<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-------------|-----------|------------|-----------|-----------|-----------|-----------|--------|----------|---------------|
|  | FR-SM 130   | 0120700 | 10        | 100       | 35         | 130         | 40        | 35         | 50        | 15        | 12        | 12        | M6     | Steel    | 3             |
|  | FR-SA 130   | 0120650 | 10        | 100       | 35         | 130         | 48        | 43         | 47.4      | 15        | 12        | 12        | M6     | Aluminum | 1.3           |





## Hard Stepped Top Jaws

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|---------------|
|  | SHB-FR 130  | 0121109 | 10        | 26        | 37.5      | 58        | 10        | 11.6      | 12        | 12        | M6     | Steel    | 0.4           |

## Serrated bars

|                                                                                     | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Material | m/piece<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|----------|-----------------|
|  | SBM-ST 100  | 0112150 | 10        | 35        | 60        | 420       | Steel    | 6.7             |

## Soft Top Jaws


|                                                                                     | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a1<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Screws | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|-----------|-----------|-----------|--------|----------|---------------|
|  | SWB-FR 130  | 0120400 | 10        | 25        | 30        | 55.5      | 3          | 11        | 12        | 12        | M6     | Steel    | 0.8           |
|  | SWB-FR 133  | 0120410 | 10        | 32        | 32        | 62        | 2          | 9         | 12        | 12        | M6     | Steel    | 1.2           |
|  | SWB-FR 132  | 0132141 | 10        | 22        | 47        | 53        |            | 9         | 12        | 12        | M6     | Steel    | 1             |
|  | FR-AL 130   | 0120600 | 10        | 25        | 45        | 53        | 3          | 9         | 12        | 12        | M6     | Aluminum | 0.4           |



Technical advice and sales: Tel. +49-7133-103-2750

# SCHUNK chuck jaws for KFD-HS 140

## T-nut

|                                                                                   | Description | ID      | S<br>[mm] | H<br>[mm] | H1<br>[mm] | b<br>[mm] | G  | Cyl.-screw | Max. adm.<br>tightening<br>torque<br>[Nm] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----------|----|------------|-------------------------------------------|
|  | NK 60       | 0147104 | 10        | 13.7      | 5.5        | 12        | M6 | M6 x 18    | 16                                        |



Technical advice and sales: Tel. +49-7133-103-2750