



SCHUNK chuck jaws for KFD-HS 160



Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	12 - 42	183	SZA-ST 16-4	0175112	12	32	40	30	15	M8	Steel	1.1


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	29 - 72	180	SZA 16-10	0122250	12	32	40	20	M5	15	M8	Steel	1
	61 - 101	178	SZA 16-11	0122251	12	32	40	20	M5	15	M8	Steel	1
	79 - 121	179	SZA 16-12	0122252	12	32	40	20	M5	15	M8	Steel	0.9


Full Grip Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	FR-SM 160	0120701	12	120	40	160	60	50	60	20	15	15	M8	Steel	6
	FR-SA 160	0120651	12	120	40	165	58	48	59.5	18	15	15	M8	Aluminum	2.1

Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB 130	0121100	12	30	38	57	10	16	15	15	M8	Steel	0.7

Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 120	0112160	12	35	60	420	Steel	6.7
	SBM-ST 121	0112163	12	40	80	420	Steel	10.2
	SBM-STA 120	0112161	12	35	60	420	Aluminum	2.4



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KFD-HS 160

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB-FR 162	0120409	12	35	40	72	3	12	15	M8	Steel	1.6
	SWB-FR 160	0120402	12	30	38	55.5		9	15	M8	Steel	1.2
	SWB-FR 161	0120403	12	30	55.5	55		9	15	M8	Steel	1.8
	FR-AL 160	0120601	12	30	55	70		9	15	M8	Aluminum	0.9

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NS 80	0140100	12	17.2	7		M8	M8 x 22	30
	NK 81	0147106	12	17.2	7	15	M8	M8 x 22	30



Technical advice and sales: Tel. +49-7133-103-2750