



SCHUNK Spannbacken für KFE 280


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	HSKN 250-280	0129102	20	44.5	54	96	12	30	26	26	M12	Stahl	2.8

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	M [mm]	a1 [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SKN 250-280	0127104	20	50	80	90	44		19	26		M12	Stahl	7.1
	SKNL 250-280	0128102	20	50	50	130	44	3.5	19	29.5	29.5	M12	Stahl	5.8

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmoment [Nm]
	NSK 250-280	0144104	20	21.5	8.5	M12	M12 x 30	70



Technische Beratung und Verkauf: Tel. +49-7133-103-2750