



# SCHUNK chuck jaws for KFG 280


## Hard Stepped Top Jaws

|                                                                                   | Description  | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|--------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|---------------|
|  | HSKN 250-280 | 0129102 | 20        | 44.5      | 54        | 96        | 12        | 30        | 26        | 26        | M12    | Steel    | 2.8           |

## Soft Top Jaws

|                                                                                   | Description  | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | M<br>[mm] | a1<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|--------------|---------|-----------|-----------|-----------|-----------|-----------|------------|-----------|-----------|-----------|--------|----------|---------------|
|                                                                                   | SKN 250-280  | 0127104 | 20        | 50        | 80        | 90        | 44        |            | 19        | 26        |           | M12    | Steel    | 7.1           |
|  | SKNL 250-280 | 0128102 | 20        | 50        | 50        | 130       | 44        | 3.5        | 19        | 29.5      | 29.5      | M12    | Steel    | 5.8           |

## T-nut

|                                                                                     | Description | ID      | S<br>[mm] | H<br>[mm] | H1<br>[mm] | G   | Cyl.-screw | Max. adm. tightening torque<br>[Nm] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----|------------|-------------------------------------|
|  | NSK 250-280 | 0144104 | 20        | 21.5      | 8.5        | M12 | M12 x 30   | 70                                  |



Technical advice and sales: Tel. +49-7133-103-2750