


SCHUNK chuck jaws for KFN 130

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SKN 130	0127101	11	26	30	55	10	15	M8	Steel	0.8

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NSK 130-160	0144101	11	15.5	6.5	M8	M8 x 20	30



Technical advice and sales: Tel. +49-7133-103-2750