



SCHUNK chuck jaws for KFN 160


Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	HSKN 160	0129100	11	26	37.5	62	10	17.5	16.5	16.5	M8	Steel	0.65

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	M [mm]	a1 [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SKN 160	0127102	11	30	55.5	67	27		17	20		M8	Steel	2.2
	SKNL 160	0128100	11	35	40	77	27	3	10	18	18	M8	Steel	1.8

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NSK 130-160	0144101	11	15.5	6.5	M8	M8 x 20	30



Technical advice and sales: Tel. +49-7133-103-2750