



SCHUNK chuck jaws for KFN 280


Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	HSKN 250-280	0129102	20	44.5	54	96	12	30	26	26	M12	Steel	2.8

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	M [mm]	a1 [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SKN 250-280	0127104	20	50	80	90	44		19	26		M12	Steel	7.1
	SKNL 250-280	0128102	20	50	50	130	44	3.5	19	29.5	29.5	M12	Steel	5.8

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NSK 250-280	0144104	20	21.5	8.5	M12	M12 x 30	70



Technical advice and sales: Tel. +49-7133-103-2750